MURR ELEKTRONIK
stay connected

MSVD POWER SOCKET NEMA


Mounting rail

USA (2× NEMA 5-15)
Screw terminals
Each socket can be loaded with 20 A, however, the total load of both sockets must be below 30 A.

[Link to Product]

Illustration





Product may differ from Image

Commercial data

ECLASS-6.0	27189217
ECLASS-6.1	27142305
ECLASS-7.0	27142305
ECLASS-8.0	27142305
ECLASS-9.0	27142305
ECLASS-10.1	27142305
ECLASS-11.1	27142305
ECLASS-12.0	27142305
ETIM-5.0	EC000020
customs tariff number	85366990
GTIN	4048879041379
Packaging unit	1

Electrical data | Supply

Operating voltage AC	125 V
Operating current max.	15 A

Installation

Connection cross section max.	6 mm²

Installation | Connection

Connection	Screw terminals SK

Mechanical data | Mounting data

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29

Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	126 mm
Width	64 mm
Depth	55 mm

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29