MURR ELEKTRONIK
stay connected

LED-INDICATOR GREEN


LED 5mm - 24V DC - IP40


(green)
24 V DC

[Link to Product]

Illustration







Product may differ from Image

Commercial data

ECLASS-6.0	27261590
ECLASS-6.1	27261501
ECLASS-7.0	27261501
ECLASS-8.0	27261501
ECLASS-9.0	27261501
ECLASS-10.1	27261501
ECLASS-11.1	27261501
ECLASS-12.0	27261501
ETIM-5.0	EC000272
customs tariff number	85318070
GTIN	4048879041133
Packaging unit	10

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29

Electrical data | Supply	
Operating voltage DC	24 V
Operating voltage DC min.	20,4 V
Operating voltage DC max.	26,4 V
Current consumption max.	18 mA
Installation | Connection	
Connection information	Faston 2.8×0.8 mm
Mechanical data | Material data	
Coating housing	chrome-plated
Material housing	Brass
Mechanical data | Mounting data	
Height	9,5 mm
Width	9,5 mm
Depth	77,5 mm
Environmental characteristics | Climatic	
Operating temperature min.	-40 °C
Operating temperature max.	70 °C

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29