MURR ELEKTRONIK
stay connected

LED-INDICATOR YELLOW


LED 5mm - 24V AC/DC - 15mA - IP67


(yellow)
24 V AC/DC
Protection IP67

Link to Product

Illustration







Product may differ from Image

Commercial data

ECLASS-6.0	27261590
ECLASS-6.1	27261501
ECLASS-7.0	27261501
ECLASS-8.0	27261501
ECLASS-9.0	27261501
ECLASS-10.1	27261501
ECLASS-11.1	27261501
ECLASS-12.0	27261501
ETIM-5.0	EC000272
customs tariff number	85318070
GTIN	4048879040747

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29

MURR ELEKTRONIK
stay connected

Packaging unit	10
Electrical data | Supply	
Operating voltage AC	24 V
Operating voltage AC min.	20,4 V
Operating voltage AC max.	26,4 V
Operating voltage DC	24 V
Operating voltage DC min.	20,4 V
Operating voltage DC max.	26,4 V
Current consumption min.	13 mA
Current consumption max.	17 mA
Installation | Connection	
Connection information	Faston 2.8×0.8 mm
Device protection | Electrical	
Degree of protection (EN IEC 60529)	IP67
Mechanical data	
Diameter LED	5 mm
Mechanical data | Material data	
Color housing	gray
Material housing	PVC
Mechanical data | Mounting data	
Diameter front panel drilling	8 mm
Height	18,5 mm
Width	12 mm
Depth	53 mm
Environmental characteristics | Climatic	
Operating temperature min.	-40 °C
Operating temperature max.	70 °C

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29