MURR ELEKTRONIK
stay connected

MOTOR SUPPRESSION SHIELDING PLUGGABLE 10M PUR


(black-halogenfree)

3× 575 V AC
VDR/star
10.0 m
PUR cable black, 4× 1.5 mm², numbered wires, halogen-free


[Link to Product]

Illustration





Varistor-suppression (star)



(without compression gland)

Product may differ from Image

Commercial data

ECLASS-6.0	27371013
ECLASS-6.1	27371013
ECLASS-7.0	27371013
ECLASS-8.0	27371013
ECLASS-9.0	27371013
ECLASS-10.1	27371013

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29

ECLASS-11.1	27371013
ECLASS-12.0	27371013
ETIM-5.0	EC000197
customs tariff number	85363010
GTIN	4048879015141
Packaging unit	1
Electrical data | Supply	
Power frequency	10 ... 400 Hz
Electrical data | Input	
Input voltage AC min.	400 V
Input voltage AC max.	575 V
Installation | Connection	
Gender	female
Installation | Pin assignment	
No. of poles	10 + PE
Mechanical data | Material data	
Coating housing	powder-coated
Material housing	Aluminum die casting
Mechanical data | Mounting data	
Height	72 mm
Width	93 mm
Depth	43 mm
Environmental characteristics | Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	60 °C

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29