MURR ELEKTRONIK
stay connected

## VALVE PLUG SUPPRESSOR FORM A - 18MM


RC and LED, 24VAC/DC/10VA/W


24 V AC/DC
RC + LED
Remove plug gasket when fitting adapter. Other LED colors on request.

[Link to Product]

### Illustration






Product may differ from Image

### Commercial data

| | |
|---|---|
| ECLASS-6.0 | 27371013 |
| ECLASS-6.1 | 27371013 |
| ECLASS-7.0 | 27371013 |
| ECLASS-8.0 | 27371013 |
| ECLASS-9.0 | 27371013 |
| ECLASS-10.1 | 27371013 |

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28

MURR ELEKTRONIK
stay connected

| | |
|---|---|
| ECLASS-11.1 | 27371013 |
| ECLASS-12.0 | 27371013 |
| ETIM-5.0 | EC000197 |
| customs tariff number | 85363010 |
| GTIN | 4048879012157 |
| Packaging unit | 1 |
| **Electrical data** | |
| Capacity CX | 20 ms |
| Holding power max. | 10 W |
| **Electrical data \| Supply** | |
| Cut-off peak voltage max. | 105 V |
| **Electrical data \| Input** | |
| Input voltage AC min. | 12 V |
| Input voltage AC max. | 30 V |
| Input voltage DC min. | 12 V |
| Input voltage DC max. | 30 V |
| **Diagnostics** | |
| Status indication LED | yellow |
| **Device protection \| Media** | |
| Flame resistance | flame retardant |
| **Mechanical data \| Material data** | |
| Coating contact | silver-plated |
| Color housing | black |
| Material housing | PA |
| Material contact | Bronze |
| **Mechanical data \| Mounting data** | |
| Height | 37 mm |
| Width | 45 mm |
| Depth | 30 mm |
| **Environmental characteristics \| Climatic** | |
| Operating temperature min. | -20 °C |
| Operating temperature max. | 60 °C |
| Housing temperature max. (EN 61347-2-13) | 130 °C |

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28