MURR ELEKTRONIK
stay connected

MODL. VARIO 6-way coupling housing type B

nickel plated aluminum

Mobile housing (round)
Aluminium
6-way

[Link to Product]

Illustration



Product may differ from Image

Commercial data	
ECLASS-6.0	27260702
ECLASS-6.1	27260708
ECLASS-7.0	27440312
ECLASS-8.0	27440312
ECLASS-9.0	27440312
ECLASS-10.1	27440312
ECLASS-11.1	27440312
ECLASS-12.0	27440312
ETIM-5.0	EC002641
customs tariff number	85389099
GTIN	4048879573009
Packaging unit	1
Mechanical data	
Operating pressure min.	-0,8 bar
Operating pressure max.	16 bar
Mechanical data | Material data	
Coating housing	nickel plated
Material housing	Aluminium
Mechanical data | Mounting data	
Looking techniques	Clip locking
Environmental characteristics | Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	120 °C

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29