MURR ELEKTRONIK
stay connected

MODL. VARIO 4-way coupling housing type B

stainless steel type 1.4404 (V4A)

Mobile housing
Stainless steel 1.4404 (V4A)
4-way

Link to Product

Illustration



Product may differ from Image

Commercial data	
ECLASS-6.0	27260702
ECLASS-6.1	27260708
ECLASS-7.0	27440312
ECLASS-8.0	27440312
ECLASS-9.0	27440312
ECLASS-10.1	27440312
ECLASS-11.1	27440312
ECLASS-12.0	27440312
ETIM-5.0	EC002641
customs tariff number	85389099
GTIN	4048879573115
Packaging unit	1
Device protection | Electrical	
Degree of protection (EN IEC 60529)	IP65, IP67, IP68
Degree of protection (ISO 20653:2013)	IP66K, IP69K
Additional condition protection degree	inserted, screwed
Mechanical data	
Operating pressure min.	-0,8 bar
Operating pressure max.	16 bar
Mechanical data | Material data	
Material housing	Stainless steel 1.4404 (V4A)
Mechanical data | Mounting data	
Mounting method	screw fixing
Environmental characteristics | Climatic	
Operating temperature min.	-20 °C

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28

Operating temperature max.	120 °C

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28