MURR ELEKTRONIK
stay connected

## LED-INDICATOR WHITE


LED 10mm - 24V DC - 20 mA - IP67


(white)
24 V DC

[Link to Product]

### Illustration






Product may differ from Image

### Commercial data

| | |
|---|---|
| ECLASS-6.0 | 27261590 |
| ECLASS-6.1 | 27261501 |
| ECLASS-7.0 | 27261501 |
| ECLASS-8.0 | 27261501 |
| ECLASS-9.0 | 27261501 |
| ECLASS-10.1 | 27261501 |
| ECLASS-11.1 | 27261501 |
| ECLASS-12.0 | 27261501 |
| ETIM-5.0 | EC000272 |
| customs tariff number | 85318070 |
| GTIN | 4048879041065 |
| Packaging unit | 10 |

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28

| | |
|---|---|
| **Electrical data \| Supply** | |
| Operating voltage DC | 24 V |
| Operating voltage DC min. | 20,4 V |
| Operating voltage DC max. | 26,4 V |
| Current consumption max. | 15 mA |
| **Installation \| Connection** | |
| Connection information | Faston 2.8×0.8 mm |
| **Mechanical data \| Material data** | |
| Coating housing | chrome-plated |
| Material housing | Brass |
| **Mechanical data \| Mounting data** | |
| Height | 16 mm |
| Width | 16 mm |
| Depth | 45 mm |
| **Environmental characteristics \| Climatic** | |
| Operating temperature min. | -30 °C |
| Operating temperature max. | 75 °C |

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28

Murrelektronik GmbH | Falkenstraße 3 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com