MURR ELEKTRONIK
stay connected

POWER DISTRIBUTOR PD4 7/8" 5 POLE


24+E male to 4 x 7/8" 5-pole female


Industry male plug 24+PE
to 4× 7/8" UNF female
5-pole

제품 링크

일러스트







실제 제품은 이미지와 다를 수 있습니다.

제품자료

ECLASS-6.0	27279219
ECLASS-6.1	27142601
ECLASS-7.0	27142601
ECLASS-8.0	27142601
ECLASS-9.0	27142601
ECLASS-10.1	27142601

이 데이터 시트에 포함된 정보는 최대한의 주의로 작성되었습니다.
2024-03-29

stay connected

ECLASS-11.1	27142606
ECLASS-12.0	27142606
ETIM-5.0	EC002585
GTIN	4048879063449
세번부호	85369010
포장단위	1
Electrical data	
Security level	SELV
Electrical data | Supply	
Operating voltage AC	50 V
Operating voltage DC	120 V
Current operating per contact max.	9 A
Device protection | Electrical	
Degree of protection (EN IEC 60529)	IP67
Additional condition protection degree	inserted, screwed
Mechanical data | Material data	
Coating housing	powder-coated
Material housing	Aluminum die casting
Mechanical data | Mounting data	
Height	165 mm
Width	70 mm
Depth	100 mm
Looking techniques	2-hand fixing (2 clamps)
Environmental characteristics | Climatic	
Operating temperature min.	-30 °C
Operating temperature max.	85 °C

이 데이터 시트에 포함된 정보는 최대한의 주의로 작성되었습니다.
2024-03-29