MURR ELEKTRONIK
stay connected

SAFETY WIRING SYSTEM


EMERGENCY OFF PUSH BUTTON with M12


E-Stop 72 2NC M12(4)
with M12 connection
4-pole
Emergency-Stop button
2 NC (positively-opening)


제품 링크

일러스트









실제 제품은 이미지와 다를 수 있습니다.

제품자료

ECLASS-6.0	27371244
ECLASS-6.1	27371244
ECLASS-7.0	27371244
ECLASS-8.0	27371244
ECLASS-9.0	27371244

이 데이터 시트에 포함된 정보는 최대한의 주의로 작성되었습니다.
2024-03-28

ECLASS-10.1	27371244
ECLASS-11.1	27371244
ECLASS-12.0	27371244
ETIM-5.0	EC002034
GTIN	4048879050654
세번부호	85365080
포장단위	1
Electrical data | Output	
Utilization category AC-15 (EN IEC 60947-5-1)	3 A @ 250 V
Utilization category DC-13 (EN IEC 60947-5-1)	2 A @ 24 V
Switching current (AC-15)	30 A
Switching current (DC-13)	2,2 A
Device protection	
Condition lifetime	load-dependent, temperature dependent
Device protection | Electrical	
Degree of protection (EN IEC 60529)	IP65
Electrical lifetime	1000000 Cycles
Device protection | Mechanical	
Mechanical endurance	1000000 Cycles
Operating life B10d	250000 Cycles
Mechanical data	
Bounce time max.	9 ms
Mechanical data | Material data	
Material contact	AgNi
Mechanical data | Mounting data	
Mounting method	screwed
Height	103 mm
Width	72 mm
Depth	91 mm
Environmental characteristics | Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	60 °C
Storage temperature min.	-25 °C
Storage temperature max.	85 °C
Technical Data | Reliability	
Lambda normally closed contact	20 %
Connection type 1	
Family construction form	M12
Gender	male
Color contact carrier	black
Coding	A
No. of poles	4
PIN 1	NC 1
PIN 2	NC 1
PIN 3	NC 2
PIN 4	NC 2

이 데이터 시트에 포함된 정보는 최대한의 주의로 작성되었습니다.
2024-03-28