MURR ELEKTRONIK
stay connected

M12 male 0° A-cod. screw terminal


5-pol., max. 0,75mm², 4 - 6mm, shielded


Male straight
M12, 5-pole
shielded
Screw terminals
Sealing range (cable Ø): 4...6 mm


제품 링크

일러스트









실제 제품은 이미지와 다를 수 있습니다.

Side 1	
Family construction form	M12
Degree of protection (EN IEC 60529)	IP67

제품자료	
ECLASS-6.0	27279221
ECLASS-7.0	27440104
ECLASS-8.0	27440104
ECLASS-9.0	27440102
ECLASS-10.1	27440102
ECLASS-11.1	27440102

Murrelektronik GmbH | Falkenstraße 3 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

stay connected

ECLASS-12.0	27440116
ETIM-5.0	EC002635
GTIN	4048879198844
세번부호	85366990
포장단위	1
Electrical data | Supply	
Operating voltage AC max.	60 V
Operating voltage DC max.	60 V
Current operating per contact max.	4 A
Installation	
Connection cross section max.	0,75 mm²
Device protection | Electrical	
Additional condition protection degree	inserted, screwed
Mechanical data | Material data	
Coating housing	nickel plated
Material housing	Brass
Mechanical data | Mounting data	
Clamping range min.	4 mm
Clamping range max.	6 mm
Environmental characteristics | Climatic	
Operating temperature min.	-40 °C
Operating temperature max.	85 °C

Murrelektronik GmbH | Falkenstraße 3 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com