MURR ELEKTRONIK
stay connected

## MOTOR SUPPRESSOR


RC, 3x575VAC/7,5kW


3× 575 V AC
RC
Suppressors for other voltages, frequencies, and motor ratings available on request. Do not use RC motor suppressors with frequency inverters.
For DIN-rail mounting use 2×Art.-No. 20900 adapter feet
approx. 500 mm, PVC cable 3× 0.75 mm²

### Ürün Linki

**örnekleme**






Ürün Image farklı olabilir

**Ticari bilgiler**

| | |
|---|---|
| ECLASS-6.0 | 27371013 |
| ECLASS-6.1 | 27371013 |
| ECLASS-7.0 | 27371013 |
| ECLASS-8.0 | 27371013 |



Murrelektronik GmbH | Falkenstraße 3 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

MURR ELEKTRONIK
stay connected

| | |
|---|---|
| ECLASS-9.0 | 27371013 |
| ECLASS-10.1 | 27371013 |
| ECLASS-11.1 | 27371013 |
| ECLASS-12.0 | 27371013 |
| ETIM-5.0 | EC000197 |
| GTIN | 4048879019484 |
| Gümrük tarife no (gtip) | 85363010 |
| Paket miktarı | 1 |
| **Electrical data \| Supply** | |
| Power frequency | 50 ... 60 Hz |
| **Electrical data \| Input** | |
| Input voltage AC | 575 V |
| **Installation** | |
| Connection cross section max. | 0,75 mm² |
| **Installation \| Connection** | |
| Family construction form | free cable end |
| **Installation \| Pin assignment** | |
| No. of poles | 3 |
| **Device protection \| Media** | |
| Flame resistance | flame retardant |
| **Mechanical data \| Material data** | |
| Combustibility class housing (UL94) | V-0 |
| Material housing | Plastic |
| Material potting compound | 2-component epoxy |
| **Mechanical data \| Mounting data** | |
| Mounting method | geschnappt |
| Suitable for mounting type | Mounting rail TH35, (EN 60715) |
| Height | 41 mm |
| Width | 41 mm |
| Depth | 41 mm |
| **Environmental characteristics \| Climatic** | |
| Operating temperature min. | -20 °C |
| Operating temperature max. | 60 °C |

Bu veri sayfasındaki bilgiler en büyük özenle hazırlandı.
Bilgilerin doğruluğu bütünlüğü ve güncelliği konusunda yükümlülük ihmali sınırlıdır. Sürüm: 2024-03-28