MURR ELEKTRONIK
stay connected

## MOTOR SUPPRESSOR


Varistor, 3x575VAC/10kW


3× 575 V AC
VDR
with (M20×1.5 mm) gland
Suppressors for other voltages, frequencies, and motor ratings available on request. Do not use RC motor suppressors with frequency inverters.

**Link to Product**

**Illustration**






Product may differ from Image

**取引条件**

| | |
|---|---|
| ECLASS-6.0 | 27371013 |
| ECLASS-6.1 | 27371013 |
| ECLASS-7.0 | 27371013 |
| ECLASS-8.0 | 27371013 |
| ECLASS-9.0 | 27371013 |

このデータシートに含まれる情報は最大限の注意を払って作成されました。
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29

| | |
|---|---|
| ECLASS-10.1 | 27371013 |
| ECLASS-11.1 | 27371013 |
| ECLASS-12.0 | 27371013 |
| ETIM-5.0 | EC000197 |
| GTIN | 4048879019101 |
| HSコード | 85363010 |
| Packaging unit | 1 |
| **Electrical data \| Input** | |
| Input voltage AC | 575 V |
| **Installation** | |
| Connection cross section max. | 1 mm² |
| **Installation \| Connection** | |
| Connection information | Single strands |
| Length single strands | 150 mm |
| Ring terminals | M6isolated |
| **Device protection \| Media** | |
| Flame resistance | flame retardant |
| **Mechanical data \| Material data** | |
| Combustibility class housing (UL94) | V-0 |
| Material housing | Plastic |
| Material potting compound | 2-component epoxy |
| **Mechanical data \| Mounting data** | |
| Mounting method | inserted |
| Suitable for mounting type | Motorklemmkasten |
| Height | 39 mm |
| Width | 39 mm |
| Depth | 44 mm |
| **Environmental characteristics \| Climatic** | |
| Operating temperature min. | -20 °C |
| Operating temperature max. | 60 °C |

このデータシートに含まれる情報は最大限の注意を払って作成されました。
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29