MURR ELEKTRONIK
stay connected

MODL. VARIO 4-way fixed housing type B

nickel plated aluminum

Stationary housing (round)
4-way
Aluminium
Screw locking
Good chemical and oil resistance (oil resistance does not apply to use with PVC cable)
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration



Product may differ from Image

取引条件	
ECLASS-6.0	27260702
ECLASS-6.1	27260708
ECLASS-7.0	27440312
ECLASS-8.0	27440312
ECLASS-9.0	27440312
ECLASS-10.1	27440312
ECLASS-11.1	27440312
ECLASS-12.0	27440312
ETIM-5.0	EC002641
GTIN	4048879572965
HSコード	85389099
Packaging unit	1

Device protection | Electrical	
Degree of protection (EN IEC 60529)	IP65, IP67, IP68
Degree of protection (ISO 20653:2013)	IP66K, IP69K
Additional condition protection degree	inserted, screwed

Mechanical data	
Operating pressure min.	-0,8 bar
Operating pressure max.	16 bar

Mechanical data | Material data	
Coating housing	powder-coated
Material housing	Aluminum die casting

Mechanical data | Mounting data

このデータシートに含まれる情報は最大限の注意を払って作成されました。
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28

Mounting method	screw fixing
Environmental characteristics | Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	120 °C

このデータシートに含まれる情報は最大限の注意を払って作成されました。
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28