MURR ELEKTRONIK
stay connected


## MODL. VARIO insert for coupling housing type B

8/6 shut-off, stainless steel type 1.4404 (V4A)

Modlink Vario
Stainless steel 1.4404 (V4A)
with shut-off
AD8

Link to Product

### Illustration



Product may differ from Image

| 取引条件 | |
|---|---|
| ECLASS-6.0 | 27260702 |
| ECLASS-6.1 | 27260708 |
| ECLASS-7.0 | 27440312 |
| ECLASS-8.0 | 27440312 |
| ECLASS-9.0 | 27440312 |
| ECLASS-10.1 | 27440312 |
| ECLASS-11.1 | 27440312 |
| ECLASS-12.0 | 27440312 |
| ETIM-5.0 | EC002641 |
| GTIN | 4048879574242 |
| HSコード | 73269098 |
| Packaging unit | 1 |

| Device protection \| Electrical | |
|---|---|
| Degree of protection (EN IEC 60529) | IP65, IP67, IP68 |
| Degree of protection (ISO 20653:2013) | IP66K, IP69K |
| Additional condition protection degree | inserted, screwed |

| Mechanical data | |
|---|---|
| Barrier | with shut-off |
| Operating pressure min. | 0 bar |
| Operating pressure max. | 16 bar |

| Mechanical data \| Material data | |
|---|---|
| Material gasket | FPM |
| Material housing | Stainless steel 1.4404 (V4A) |

| Mechanical data \| Mounting data |
|---|

このデータシートに含まれる情報は最大限の注意を払って作成されました。
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29

| | |
|---|---|
| Outer diameter hose | 8 mm |
| **Environmental characteristics \| Climatic** | |
| Operating temperature min. | -20 °C |
| Operating temperature max. | 120 °C |

このデータシートに含まれる情報は最大限の注意を払って作成されました。
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29