## MSVD POWER SOCKET VDE

Mounting rail

Art.No.: 67900
Weight: 0.113 kg
Country of origin: HU
Model designation: MSVD Steckdose VDE o.LED Anschluss vorne

Germany (VDE) white
Screw terminals

[Link to Product]

### Illustration




Product may differ from Image

### Commercial data

| | |
|---|---|
| URL webshop | https://shop.murrelektronik.com/67900 |
| GTIN | 4048879041447 |
| EU-Customs tariff number | 85366990 |
| US-Customs tariff number | 8536694020 |
| ECLASS-6.0 | 27189217 |
| ECLASS-6.1 | 27142305 |
| ECLASS-7.0 | 27142305 |
| ECLASS-7.1 | 27142305 |
| ECLASS-8.0 | 27142305 |
| ECLASS-8.1 | 27142305 |
| ECLASS-9.0 | 27142305 |
| ECLASS-9.1 | 27142305 |
| ECLASS-10.0.1 | 27142305 |
| ECLASS-10.1 | 27142305 |
| ECLASS-11.0 | 27142305 |
| ECLASS-11.1 | 27142305 |
| ECLASS-12.0 | 27142305 |
| ECLASS-13.0 | 27142305 |
| ECLASS-14.0 | 27142305 |
| ETIM-5.0 | EC000020 |

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18

| | |
|---|---|
| ETIM-6.0 | EC000020 |
| ETIM-7.0 | EC000020 |
| ETIM-8.0 | EC000020 |
| ETIM-9.0 | EC000020 |
| ETIM-10.0 | EC000020 |
| customs tariff number | 85366990 |
| EAN | 4048879041447 |
| Packaging unit | 1 |
| **Mechanical data \| Mounting data** | |
| Height | 81 mm |
| Width | 45 mm |
| Depth | 66 mm |
| **Germany (VDE)** | |
| Connection type | Screw terminals SK |
| No. of poles | 2 + PE |
| Connections per pole | 2 |
| Protection contact present | Yes |
| Connection cross section max. | 6 mm² |
| AWG number max. | 10 |
| Mounting method | Snap-in connector |
| Suitable for mounting type | Mounting rail TH35 |
| Operating voltage AC | 250 V |
| Operating current | 16 A |

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18