MB CAP ULTRA ADD-ON-MODULE

IN: 0-26,4VDC OUT:0-26,4VDC/3A for max.1A/21S

Art.No.: 85462
Weight: 0.600 kg
Country of origin: DE
Model designation: MB Cap Ultra Add-on-module 3/24 1A/21S

INPUT: 24 V DC (SELV/PELV)
OUTPUT: max. 3 A
12 s (3 A); 36 s (1 A)

Link to Product

Illustration





Product may differ from Image

Commercial data

URL Webshop	https://shop.murrelektronik.com/85462
GTIN	4048879079792
EU-Customs tariff number	85322900
US-Customs tariff number	8532290040

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-09-10

ECLASS-6.0	27049190
ECLASS-6.1	27049201
ECLASS-7.0	27049201
ECLASS-7.1	27049201
ECLASS-8.0	27049201
ECLASS-8.1	27049201
ECLASS-9.0	27040705
ECLASS-9.1	27040705
ECLASS-10.0.1	27040692
ECLASS-10.1	27040692
ECLASS-11.0	27040692
ECLASS-11.1	27040692
ECLASS-12.0	27040692
ECLASS-13.0	27040692
ECLASS-14.0	27040692
ETIM-5.0	EC002584
ETIM-6.0	EC002584
ETIM-7.0	EC002584
ETIM-8.0	EC002584
ETIM-9.0	EC002584
ETIM-10.0	EC002584
customs tariff number	85322900
EAN	4048879079792
Packaging unit	1
Electrical data | Supply	
Protective measure	SELV/PELV
Electrical data | Input	
Input voltage DC min.	0 V
Input voltage DC max.	26,4 V
Current input AC	3 A
Efficiency	90 %
Electrical data | Output	
Output voltage adjustable	Yes
Output voltage DC min.	0 V
Output voltage DC max.	26,4 V
Output current	3 A
Buffer time min.	12 s @ 3 A
Buffer time max.	36 s @ 1 A
Mechanical data | Mounting data	
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)
Environmental characteristics | Electromagnetic compatibility	
Immunitiy standard for industrial environments (IEC 61000-6-2)	compliant
Environmental characteristics | Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	60 °C
Ambient temperature (storage, transport)	-20 °C … 60 °C
Conformity	
Product standard	EN/IEC 60950-1, EN/IEC 50178

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-09-10