EXACT12, 4XM12, 4 POLE

Conn.M12 8pole

Art.No.: 8000-84470-0000000
Weight: 0.107 kg
Country of origin: DE
Model designation: MVP12N-NS4V

4-way
4-pole (port 3+4)
5-pole (port 1+2)
M12 plug connection, 8-pole
With LED for digital PNP-signals 24 V DC
Plastic housings with good resistance against chemicals and oils.

Link to Product

Illustration







The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18



Product may differ from Image

Commercial data	
URL webshop	https://shop.murrelektronik.com/8000-84470-0000000
GTIN	4048879323086
EU-Customs tariff number	85366990
US-Customs tariff number	8536694020
ECLASS-6.0	27279219
ECLASS-6.1	27279219
ECLASS-7.0	27279219
ECLASS-7.1	27279219
ECLASS-8.0	27279219
ECLASS-8.1	27279219
ECLASS-9.0	27440111
ECLASS-10.0.1	27440111
ECLASS-10.1	27440111
ECLASS-11.0	27440111
ECLASS-11.1	27440111
ECLASS-12.0	27440111
ECLASS-13.0	27440111
ECLASS-14.0	27440111
ETIM-5.0	EC002585
ETIM-6.0	EC002585
ETIM-7.0	EC002585
ETIM-8.0	EC002585
ETIM-9.0	EC002585
ETIM-10.0	EC002585
customs tariff number	85366990
EAN	4048879323086
Packaging unit	1

Electrical data | Supply	
Operating voltage DC	24 V
Current operating per contact max.	2 A
Total current max.	2 A

Device protection | Electrical	

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18

Degree of protection (EN IEC 60529)	IP67, IP65
Device protection | Media	
Flame resistance	flame retardant
Mechanical data | Material data	
Housing	Plastic
Environmental characteristics | Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	70 °C
Connection type 2-2	
Family construction form	M12
No. of poles	8
Coding	A
Gender	Male
Color contact carrier	black
PIN 5	+
Family construction form	M8
No. of poles	4
Coding	A
Gender	Female
Color contact carrier	black
PIN 1	+
PIN 2	n.c.
PIN 3	-
PIN 4	NO S 1

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18