EXACT12, 8XM12, 4 POLE CAP, PLUG. SCREW-TERM.

Art.No.: 8000-88450-0000000
Weight: 0.206 kg
Country of origin: DE
Model designation: MVP12N-FN8V

8-way, 4-pole
Form PNP
Screw plug-in terminals
Plastic housings with good resistance against chemicals and oils.
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration







The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-09-10





Product may differ from Image

Commercial data	
URL Webshop	https://shop.murrelektronik.com/8000-88450-0000000
GTIN	4048879054164
EU-Customs tariff number	85366990
US-Customs tariff number	8536694020
ECLASS-6.0	27143423
ECLASS-6.1	27279219
ECLASS-7.0	27279219
ECLASS-7.1	27279219
ECLASS-8.0	27279219
ECLASS-8.1	27279219
ECLASS-9.0	27440111
ECLASS-10.0.1	27440111
ECLASS-10.1	27440111
ECLASS-11.0	27440111
ECLASS-11.1	27440111
ECLASS-12.0	27440111
ECLASS-13.0	27440111
ECLASS-14.0	27440111
ETIM-5.0	EC002585
ETIM-6.0	EC002585
ETIM-7.0	EC002585
ETIM-8.0	EC002585
ETIM-9.0	EC002585
ETIM-10.0	EC002585
customs tariff number	85366990
EAN	4048879054164
Packaging unit	1

Electrical data | Supply	
Operating voltage DC	24 V
Current operating per contact max.	4 A
Total current max.	8 A

Installation

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-09-10

Connection cross section max.	1,5 mm²
AWG number max.	16
Installation | Connection	
Connection	Screw plug-in terminals
Device protection | Electrical	
Degree of protection (EN IEC 60529)	IP67, IP65
Device protection | Media	
Flame resistance	flame retardant
Mechanical data | Material data	
housing	Plastic
Environmental characteristics | Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	70 °C
Connection type 2	
Family construction form	Cap
No. of poles	14
Family construction form	M12
No. of poles	4
Coding	A
Gender	female
Color contact carrier	black
PIN 1	+
PIN 2	n.c.
PIN 3	-
PIN 4	NO S 1
PIN 5	PE

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-09-10