


MIRO 6.2 OPTO-COUPLER MODULE

IN: 230 VAC/DC - OUT: 253 VAC/DC / 0,5 A

Screw terminals
Multi voltage output
Transistor 0.5 A
24...230 V AC/DC

[Link to Product](#)

Illustration



Product may differ from Image



取引条件	
ECLASS-6.0	27371604
ECLASS-6.1	27371604
ECLASS-7.0	27371604
ECLASS-8.0	27371604
ECLASS-9.0	27371604
ECLASS-10.1	27371604

ECLASS-11.1	27371604
ECLASS-12.0	27371604
ETIM-5.0	EC001504
GTIN	4048879026710
HSコード	85414900
Packaging unit	1
Electrical data Input	
Input voltage AC min.	12 V
Input voltage AC max.	230 V
Input voltage OFF AC min.	0 V
Input voltage OFF AC max.	5 V
Input voltage OFF DC min.	0 V
Input voltage OFF DC max.	5 V
Input voltage DC min.	12 V
Input voltage DC max.	230 V
Input current max.	5 mA
Electrical data Output	
Switch off delay max.	15 ms
Switch on delay max.	5 ms
Quiescent current OFF max.	0,02 mA
Switching frequency max.	2,5 Hz
Voltage switching AC min.	10 V
Switching voltage AC max.	230 V
Voltage switching DC min.	10 V
Switching voltage DC max.	230 V
Switching current min.	1 mA
Switching current max.	0,5 A
Voltage drop AC max.	2,6 V
Voltage drop DC max.	2,6 V
Diagnostics	
Status indication LED	yellow
Device protection Electrical	
Rated insulation voltage	2750 V
Device protection Media	
Flame resistance	flame retardant
Mechanical data Material data	
Color housing	black
Material housing	Plastic
Mechanical data Mounting data	
Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	78 mm
Width	6,2 mm
Depth	70 mm
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	60 °C
Connection type 4	
Connection	Screw terminals SK
Family construction form	terminal
Gender	female

Color contact carrier	black
No. of poles	1
PIN 1	13
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
Color contact carrier	black
No. of poles	1
PIN 1	14
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
Color contact carrier	black
No. of poles	1
PIN 1	A 1
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
Color contact carrier	black
No. of poles	1
PIN 1	A 2