



EXACT8, 8XM8, 4 POLE PLUG. CAP, SPRING-TERM.

3.0m PUR 16x0,34+2x0,75, UL/CSA


8-way, 4-pole  
3.0 m  
Further cable lengths on request.  
Plastic housings with good resistance against chemicals and oils.  
The resistance to aggressive media should be individually tested for your application. Further details on request.

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



| 제품자료       |          |
|------------|----------|
| ECLASS-6.0 | 27143423 |
| ECLASS-6.1 | 27279219 |
| ECLASS-7.0 | 27279219 |
| ECLASS-8.0 | 27279219 |
| ECLASS-9.0 | 27440108 |

|                                          |                                                                                                                                                                        |
|------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| ECLASS-10.1                              | 27440108                                                                                                                                                               |
| ECLASS-11.1                              | 27440108                                                                                                                                                               |
| ECLASS-12.0                              | 27440108                                                                                                                                                               |
| ETIM-5.0                                 | EC002585                                                                                                                                                               |
| GTIN                                     | 4048879054386                                                                                                                                                          |
| 세번부호                                     | 85444290                                                                                                                                                               |
| 포장단위                                     | 1                                                                                                                                                                      |
| Electrical data   Supply                 |                                                                                                                                                                        |
| Operating voltage DC                     | 24 V                                                                                                                                                                   |
| Current operating per contact max.       | 2 A                                                                                                                                                                    |
| Total current max.                       | 8 A                                                                                                                                                                    |
| Industrial communication                 |                                                                                                                                                                        |
| Number of signals per port               | 2                                                                                                                                                                      |
| Installation   Connection                |                                                                                                                                                                        |
| Mounting set                             | M8 x 1                                                                                                                                                                 |
| Device protection   Electrical           |                                                                                                                                                                        |
| Degree of protection (EN IEC 60529)      | IP67                                                                                                                                                                   |
| Additional condition protection degree   | screwed, mounted                                                                                                                                                       |
| Device protection   Media                |                                                                                                                                                                        |
| Flame resistance                         | flame retardant                                                                                                                                                        |
| Mechanical data   Material data          |                                                                                                                                                                        |
| Material housing                         | Plastic                                                                                                                                                                |
| Mechanical data   Mounting data          |                                                                                                                                                                        |
| Mounting method                          | Schraubgewinde                                                                                                                                                         |
| Environmental characteristics   Climatic |                                                                                                                                                                        |
| Operating temperature min.               | -20 °C                                                                                                                                                                 |
| Operating temperature max.               | 80 °C                                                                                                                                                                  |
| Additional condition temperature range   | depending on cable quality                                                                                                                                             |
| Installation   Cable                     |                                                                                                                                                                        |
| Cable identification                     | 396                                                                                                                                                                    |
| Jacket Color                             | gray                                                                                                                                                                   |
| Type of Certificate                      | cURus, CSA                                                                                                                                                             |
| Amount stranding                         | 1                                                                                                                                                                      |
| Stranding                                | 6 wires around Core filler twisted                                                                                                                                     |
| Amount stranding (type 2)                | 1                                                                                                                                                                      |
| Stranding (type 2)                       | 12 wires around Stranding combination twisted                                                                                                                          |
| Banding                                  | Fleece                                                                                                                                                                 |
| Filler                                   | yes                                                                                                                                                                    |
| wire arrangement                         | gray-pink, red-blue, green-white, brown-green, black, violet, (brown, blue, brown-gray, gray-white, brown-yellow, yellow-white, red, pink, gray, yellow, green, white) |
| Cable weigth                             | 143 g/m                                                                                                                                                                |
| Material jacket                          | PUR                                                                                                                                                                    |
| Shore hardness jacket                    | 89 ± 5 Shore A                                                                                                                                                         |
| Freedom from ingredients (jacket)        | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free, LABS-free                                                                                              |
| Outer-diameter (jacket)                  | 10,4 mm                                                                                                                                                                |
| Tolerance outer diameter (sheath)        | ± 5 %                                                                                                                                                                  |
| Material wire insulation                 | TPE-E                                                                                                                                                                  |
| Amount wires                             | 16                                                                                                                                                                     |
| Outer diameter insulation                | 1,5 mm                                                                                                                                                                 |
| Outer diameter tolerance core insulation | ± 5 %                                                                                                                                                                  |
| Shore hardness wire insulation           | 55 ± 5 Shore D                                                                                                                                                         |

|                                                   |                                                      |
|---------------------------------------------------|------------------------------------------------------|
| Ingredient freeness wire insulation               | lead-free, cadmium-free, CFC-free, halogen-free      |
| Traversing distance (C-track)                     | 5 m @ 25 °C   horizontal                             |
| Amount strands (wire)                             | 42                                                   |
| Diameter of single wires                          | 0,1 mm                                               |
| Conductor crossection (wire)                      | 0,34 mm²                                             |
| Material conductor wire                           | Stranded copper wire, bare                           |
| Conductor type (wire)                             | strand class 6                                       |
| Material wire insulation (Data)                   | TPE-E                                                |
| Outer diameter wire insulation (Data)             | 1,8 mm                                               |
| Tolerance outer diameter wire insulation (data)   | ± 5 %                                                |
| Shore hardness wire insulation (Data)             | 55 ± 5 Shore D                                       |
| Ingredient freeness wire insulation (Data)        | lead-free, cadmium-free, CFC-free, halogen-free      |
| Amount wires (Data)                               | 2                                                    |
| Amount strands wire (Data)                        | 42                                                   |
| Diameter of single wires (Data)                   | 0,15 mm                                              |
| Conductor crossection wire (Data)                 | 0,75 mm²                                             |
| Material conductor wire (Data)                    | Stranded copper wire, bare                           |
| Wire conductor type (Data)                        | strand class 6                                       |
| Max. rated voltage (conductor - conductor)        | 300 V                                                |
| Max. rated voltage (conductor - ground)           | 300 V                                                |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                    |
| Current load capacity min. wire                   | 4 A                                                  |
| Current load capacity min. Wire (Data)            | 12 A                                                 |
| Electrical resistance line constant wire          | 57 Ω/km @ 20 °C                                      |
| Electrical resistance coating wire (Data)         | 26 Ω/km @ 20 °C                                      |
| AC withstand voltage (wire - wire)                | 2 kV @ 60 s                                          |
| Power frequency withstand voltage (wire - jacket) | 2 kV @ 60 s                                          |
| Min. operating temperature (static)               | -40 °C                                               |
| Max. operating temperature (fixed)                | 80 °C                                                |
| Operating temperature min. (dynamic)              | -5 °C                                                |
| Operating temperature max. (dynamic)              | 80 °C                                                |
| Flame resistance                                  | UL 1581 § 1090   UL 1581 § 1100 FT2   IEC 60332-2-2  |
| chemical resistance                               | Good, application-related testing                    |
| Gasoline resistance                               | Good, application-related testing                    |
| Oil resistance                                    | Good, application-related testing   DIN EN 60811-404 |
| Bending radius (installation)                     | x Outer diameter                                     |
| Bending radius (fixed)                            | 7,5 x Outer diameter                                 |
| Bending radius (dynamic)                          | 10 x Outer diameter                                  |
| Travel speed (C-track)                            | 5 Mio. @ 25 °C                                       |

#### Connection type 2

|                          |                |
|--------------------------|----------------|
| Family construction form | free cable end |
| No. of poles             | 10             |
| Family construction form | M8             |
| Gender                   | female         |
| Color contact carrier    | black          |
| Coding                   | A              |
| No. of poles             | 4              |
| PIN 1                    | +              |
| PIN 2                    | S 2            |
| PIN 3                    | -              |
| PIN 4                    | S 1            |