



RMME 11/48 AC/DC INPUT RELAY

Product discontinued, no alternative

1 relay; 1 NO contact
6 A
48 V AC/DC
Screw terminals

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27371001
ECLASS-7.0	27371001
ECLASS-8.0	27371001
ECLASS-9.0	27371001
ETIM-5.0	EC001437
customs tariff number	85364900

GTIN	4048879027472
------	---------------

Packaging unit	1
----------------	---

Electrical data | Input

Input voltage AC	48 V
------------------	------

Input voltage AC min.	40 V
-----------------------	------

Input voltage AC max.	53 V
-----------------------	------

Input voltage DC	48 V
------------------	------

Input voltage DC min.	40 V
-----------------------	------

Input voltage DC max.	53 V
-----------------------	------

Input current	10 mA
---------------	-------

Electrical data | Output

Utilization category AC-15 (EN IEC 60947-5-1)	4 A @ 24 V, 4 A @ 110 V, 4 A @ 230 V
---	--------------------------------------

Utilization category DC-13 (EN IEC 60947-5-1)	2 A @ 24 V, 0,25 A @ 110 V, 0,1 A @ 230 V
---	---

Switching frequency max.	15 Hz
--------------------------	-------

Power rating AC max.	1500 VA
----------------------	---------

Power rating DC max.	120 W
----------------------	-------

Switching voltage AC max.	250 V
---------------------------	-------

Switching voltage DC max.	250 V
---------------------------	-------

Switching current DC	1 mA
----------------------	------

Switching current max.	6 A
------------------------	-----

Switching capacity AC-12 (EN IEC 60947-5-1)	6 A (24/110/230 V AC)
---	-----------------------

Diagnostics

Status indication LED	yellow
-----------------------	--------

Device protection

Condition lifetime	load-dependent
--------------------	----------------

Device protection | Electrical

Rated surge voltage	1,5 kV
---------------------	--------

Electrical lifetime	100000000 Cycles
---------------------	------------------

Device protection | Mechanical

Mechanical endurance	100000000 Cycles
----------------------	------------------

Mechanical data

Drop-out time max.	10 ms
--------------------	-------

Response time max.	10 ms
--------------------	-------

Bounce time max.	1 ms
------------------	------

Mechanical data | Material data

Material contact	AG Ni hv
------------------	----------

Mechanical data | Mounting data

Mounting method	geschnappt
-----------------	------------

Suitable for mounting type	Mounting rail TH35, G32, (EN 60715)
----------------------------	-------------------------------------

Height	56 mm
--------	-------

Width	12 mm
-------	-------

Depth	65 mm
-------	-------

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
----------------------------	--------

Operating temperature max.	60 °C
----------------------------	-------

Connection type 2

Connection	Screw terminals SK
------------	--------------------

Family construction form	terminal
--------------------------	----------

Gender	female
--------	--------

No. of poles	2
--------------	---

PIN 1	13
PIN 2	14
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
No. of poles	2
PIN 1	A 1
PIN 2	A 2