

CAN-PLUG-MALE (SUB-D) 90°

Screw terminals up to 1Mbps/s

Bus connection plug 90°
SUB-D9 (female), screw terminals
max. 1 Mbit/s with switchable terminal resistors
CANopen
Plastic housings with good resistance against chemicals and oils.
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration



Product may differ from Image

Commercial data	
ECLASS-6.0	27279221
ECLASS-7.0	27440104
ECLASS-8.0	27440104
ECLASS-9.0	27440102
ECLASS-10.1	27242692
ECLASS-11.1	27242692
ECLASS-12.0	27242692
ETIM-5.0	EC002584
customs tariff number	85366990
GTIN	4048879049825
Packaging unit	1
Electrical data	
Terminating resistor	connectable, integrated
Industrial communication	
Data transmission rate max.	1 MBit/s
Installation	
Connection cross section max.	1 mm²
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP20
Mechanical data Mounting data	
Height	65 mm

Width	48 mm
-------	-------

Depth	16 mm
-------	-------

Environmental characteristics | Climatic

Operating temperature min.	0 °C
----------------------------	------

Operating temperature max.	60 °C
----------------------------	-------

Storage temperature min.	-25 °C
--------------------------	--------

Storage temperature max.	80 °C
--------------------------	-------

Important installation notes

Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
-----------------------	---

Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
------------------------	---

Connection type 2

Family construction form	D-Sub
--------------------------	-------

Gender	female
--------	--------

No. of poles	9
--------------	---

PIN 2	CAN_L
-------	-------

PIN 3	CAN_GND
-------	---------

PIN 5	CAN_SHLD
-------	----------

PIN 6	0 V
-------	-----

PIN 7	CAN_H
-------	-------

PIN 9	CAN V +
-------	---------

Connection	Screw terminals SK
------------	--------------------

Family construction form	terminal
--------------------------	----------

Gender	female
--------	--------

No. of poles	6
--------------	---