

MPOT POTENTIOMETER MODULE

1K-Ohm/270 degree

270° potentiometer



1 kΩ

The 10-turn potentiometer has a decimal scale and locking lever

The potentiometer modules are fitted with standard values. They are available as 270° potentiometer and as 10-turn potentiometer with fine adjustment. They can be operated with 10 V DC or 24 V DC. A resistor reduces the voltage so that a 24 V DC voltage can be reduced to operate between approx. 0...11 V. The connection is via terminals.

Link to Product

Illustration



Product may differ from Image

| Commercial data | |
|-----------------|----------|
| ECLASS-6.0 | 27371227 |
| ECLASS-6.1 | 27371227 |
| ECLASS-7.0 | 27371227 |
| ECLASS-8.0 | 27371227 |
| ECLASS-9.0 | 27371227 |
| ECLASS-10.1 | 27371227 |
| ECLASS-11.1 | 27371227 |
| ECLASS-12.0 | 27371227 |
| ETIM-5.0 | EC001027 |

| | |
|---|---------------------------|
| customs tariff number | 85334010 |
| GTIN | 4048879041690 |
| Packaging unit | 1 |
| Electrical data | |
| Power max. | 1 W |
| Linearity | ±3 % |
| Resistance | 1 kΩ |
| Resistance tolerance | 20 % |
| Electrical data Input | |
| Power loss max. | 0,25 W |
| Mechanical data Mounting data | |
| Mounting method | geschnappt |
| Suitable for mounting type | mounting rail, (EN 60715) |
| Height | 75 mm |
| Width | 45 mm |
| Depth | 65 mm |
| Environmental characteristics Climatic | |
| Operating temperature min. | 0 °C |
| Operating temperature max. | 60 °C |