


MST SINGLE-PHASE CONTROL AND ISOLATION TRANSFORMER

P:250VA IN:200/230/460VAC OUT:24/115VAC

Single-phase - Control and Isolation Transformers
20 VA (24 V AC)
300 VA (115 V AC)
Other voltages on request.

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.

제품자료	
ECLASS-6.0	27031202
ECLASS-7.0	27031202
ECLASS-8.0	27031202
ECLASS-9.0	27031202
ETIM-5.0	EC002485
GTIN	4048879073813
세번부호	85043180
포장단위	1

Electrical data Supply	
Power frequency	50 ... 60 Hz

Electrical data Input	
Input voltage 1 AC	200 V
Input voltage 2 AC	230 V
Input voltage 3 AC	460 V
Input current at input voltage 2 AC	1,23 A
Input current at input voltage 3 AC	0,61 A
Inrush current at input voltage 2	18,5 A
Inrush current at input voltage 3	8,03 A
Short-circuit current at input voltage 2	30,1 A
Short-circuit current at input voltage 3	13,1 A
Electrical data Output	
Output voltage AC 1	24 V
Output voltage AC 2	115 V
Output voltage adjustable	no
Power rating AC max.	250 VA
Device protection Electrical	
Insulation test voltage input - output	4,8 kV
Mechanical data Mounting data	
Suitable for mounting type	Schlüssellochaufhängung
Mounting dimension a	75,3 mm
Mounting dimension b	84 mm
Mounting dimension c	5,8 mm
Height	105 mm
Width	96 mm
Depth	91 mm
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	40 °C
Storage temperature min.	-40 °C
Storage temperature max.	80 °C
Conformity	
Product standard	EN 61558-2-6, EN 62041 category 0
Connection type 3	
Connection type 1	Input
Connection type 2	Output
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
No. of poles	4
PIN 2	200 V
PIN 3	230 V
PIN 4	460 V
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
No. of poles	4
PIN 2	24 V DC
PIN 4	115 V
Connection	Screw terminals SK
Family construction form	terminal
Gender	female

Color contact carrier	metallic
No. of poles	1
PIN 1	PE