

**MODLINK MSDD SINGLE COMBI INSERT SWISS**

2x data cutout

1× Swiss  
2× RJ45 cut-out

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data

|                       |               |
|-----------------------|---------------|
| ECLASS-6.0            | 27189217      |
| ECLASS-6.1            | 27189217      |
| ECLASS-7.0            | 27189217      |
| ECLASS-8.0            | 27189217      |
| ECLASS-9.0            | 27182806      |
| ECLASS-10.1           | 27182806      |
| ECLASS-11.1           | 27182806      |
| ECLASS-12.0           | 27182806      |
| ETIM-5.0              | EC000020      |
| customs tariff number | 85366990      |
| GTIN                  | 4048879601061 |
| Packaging unit        | 1             |

Device protection | Electrical

|                                     |      |
|-------------------------------------|------|
| Degree of protection (EN IEC 60529) | IP20 |
|-------------------------------------|------|

Mechanical data | Mounting data

|        |         |
|--------|---------|
| Height | 87,5 mm |
| Width  | 50,7 mm |
| Depth  | 43 mm   |

Environmental characteristics | Climatic

|                            |       |
|----------------------------|-------|
| Operating temperature min. | -5 °C |
| Operating temperature max. | 50 °C |

|                          |        |
|--------------------------|--------|
| Storage temperature min. | -10 °C |
|--------------------------|--------|

|                          |       |
|--------------------------|-------|
| Storage temperature max. | 60 °C |
|--------------------------|-------|

**Shielding plate**

|                        |                  |
|------------------------|------------------|
| Connection information | Threaded hole M4 |
|------------------------|------------------|

|                   |        |
|-------------------|--------|
| Tightening torque | 0,9 Nm |
|-------------------|--------|

**Swiss**

|                               |                     |
|-------------------------------|---------------------|
| Connection cross section max. | 1,5 mm <sup>2</sup> |
|-------------------------------|---------------------|

|                 |    |
|-----------------|----|
| AWG number max. | 16 |
|-----------------|----|

|                      |       |
|----------------------|-------|
| Operating voltage AC | 250 V |
|----------------------|-------|

|                   |      |
|-------------------|------|
| Operating current | 10 A |
|-------------------|------|

|            |                           |
|------------|---------------------------|
| Connection | Spring clamp terminals FK |
|------------|---------------------------|

|              |        |
|--------------|--------|
| No. of poles | 2 + PE |
|--------------|--------|

|                      |   |
|----------------------|---|
| Connections per pole | 2 |
|----------------------|---|

|                            |     |
|----------------------------|-----|
| Protection contact present | yes |
|----------------------------|-----|