

M8 female 0° D-cod. screw terminal4-pol., 0,14-0,5mm², max. 6,7mm, shielded, CAT5e

Female straight

M8, 4-pole



D-coded

shielded


Screw terminals

Connection cross section: 0.14...0.5 mm²**Ürün Linki**

örnekleme



Ürün Image farklı olabilir

**Side 1**

Family construction form	M8
Material contact	Copper alloy
Width across flats	SW13
Degree of protection (EN IEC 60529)	IP67

Ticari bilgiler

ECLASS-6.0	27279218
ECLASS-7.0	27279218
ECLASS-8.0	27279218
ECLASS-9.0	27060311
ETIM-5.0	EC001855
GTIN	4065909035030
Gümrük tarife no (gtip)	85366990
Paket miktarı	1

Electrical data | Supply

Operating voltage AC	50 V
Operating voltage DC	60 V
Current operating per contact max.	4 A

Diagnostics

Status indication LED	no
-----------------------	----

Installation

Connection cross section min.	0,14 mm ²
Connection cross section max.	0,5 mm ²

Installation | Connection

Tightening torque	0,4 Nm
Mounting set	M8 x 1
Family construction form	M8
Mating cycles min.	100

Installation | Pin assignment

Coding	D
--------	---

Device protection

Shielded	yes
----------	-----

Device protection | Electrical

Additional condition protection degree	inserted, screwed
Pollution Degree	3/2
Insulation resistance min.	100 MΩ

Mechanical data | Material data

Coating contact	nickel plated
-----------------	---------------

Mechanical data | Mounting data

Mounting method	inserted, screwed, Shaking protection
Clamping range max.	6,7 mm

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	85 °C

Important installation notes

Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.