

**SVS Eco valve plug C-8mm screw terminal**

2-pol. + PE, max. 0,5mm², 4 -6mm

Form C (8 mm)

250 V AC/DC

without components

metric




field-wireable

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

**Ürün Linki**

örnekleme



Ürün Image farklı olabilir

**Side 1**

|                                     |                   |
|-------------------------------------|-------------------|
| Mounting method                     | inserted, screwed |
| Degree of protection (EN IEC 60529) | IP65              |

**Ticari bilgiler**

|            |          |
|------------|----------|
| ECLASS-6.0 | 27279221 |
| ECLASS-7.0 | 27440104 |
| ECLASS-8.0 | 27440104 |
| ECLASS-9.0 | 27440102 |

|                         |               |
|-------------------------|---------------|
| ECLASS-10.1             | 27440105      |
| ECLASS-11.1             | 27440105      |
| ECLASS-12.0             | 27440105      |
| ETIM-5.0                | EC002062      |
| GTIN                    | 4048879187015 |
| Gümrük tarife no (gtip) | 85366990      |
| Paket miktarı           | 1             |

**Electrical data | Supply**

|                                    |       |
|------------------------------------|-------|
| Operating voltage AC max.          | 250 V |
| Operating voltage DC max.          | 250 V |
| Current operating per contact max. | 6 A   |

**Installation**

|                               |                     |
|-------------------------------|---------------------|
| Connection cross section max. | 0,5 mm <sup>2</sup> |
|-------------------------------|---------------------|

**Installation | Connection**

|                                  |           |
|----------------------------------|-----------|
| Tightening torque                | 0,4 Nm    |
| Tightening torque clamping screw | 0,2 Nm    |
| Mounting set                     | M12 x 1.5 |

**Installation | Pin assignment**

|              |        |
|--------------|--------|
| No. of poles | 2 + PE |
|--------------|--------|

**Device protection | Electrical**

|                                        |                   |
|----------------------------------------|-------------------|
| Additional condition protection degree | inserted, screwed |
|----------------------------------------|-------------------|

**Mechanical data | Material data**

|                 |     |
|-----------------|-----|
| Material gasket | NBR |
|-----------------|-----|

**Mechanical data | Mounting data**

|                     |      |
|---------------------|------|
| fastening screw     | M2.5 |
| Clamping range min. | 4 mm |
| Clamping range max. | 6 mm |

**Environmental characteristics | Climatic**

|                            |        |
|----------------------------|--------|
| Operating temperature min. | -40 °C |
| Operating temperature max. | 90 °C  |

**Important installation notes**

|                        |                                                                                                                                                       |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| Note on strain relief  | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.                                                   |
| Note on bending radius | <b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |