

## Adaptor M12 male on rear / MSUD valve plug A-18mm

5-pol. A-cod.

Art.No.: 7000-41441-0000000

Weight: 0.03

Country of origin: CZ

Model designation: MSZLE-C

Form A (18 mm) - M12, connector at the rear

for pressure switches 24 V DC ±25% LED (yellow/green)

5-pole


Plastic housings with good resistance against chemicals and oils.


The resistance to aggressive media should be individually tested for your application. Further details on request.


## **Link to Product**

## Illustration












stay connected



Product may differ from Image









Side 1	
Family construction form	Valve connector form A
Tightening torque	0,4 Nm
Side 2	
Family construction form	M12
Tightening torque	0,6 Nm
Commercial data	
URL Webshop	https://shop.murrelektronik.com/7000-41441-0000000
customs tariff number	85366990
EAN	4048879144612
Packaging unit	1
Electrical data   Supply	
Operating voltage DC	24 V
Operating voltage DC min.	18 V
Operating voltage DC max.	30 V
Current operating per contact max.	4 A
Diagnostics	
Status indication LED	green, yellow
Installation   Connection	
Mounting set	M3x31
Installation   Pin assignment	
No. of poles	PE
Device protection   Electrical	
Degree of protection (EN IEC 60529)	IP67
Additional condition protection degree	inserted, screwed
Rated surge voltage	0,8 kV
Material group (IEC 60664-1)	I
Environmental characteristics   Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	85 °C
Important installation notes	

The information in this Product-PDF has been compiled with the utmost care. Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-11-26



Note on bending radius

Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.

Note on strain relief

Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.