

Adaptor M12 male on top / MSUD valve plug A-18mm

5-pol. A-cod.

Art.No.: 7000-41321-0000000

Weight: 0.032

Country of origin: CZ

Model designation: MSZLI-A

Form A (18 mm) – M12, connector top entry

24 V DC $\pm 25\%$




for pressure switches


LED (yellow/green)

5-pole

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)
Illustration




Product may differ from Image

**Side 1**

Family construction form	Valve connector form A
Tightening torque	0,4 Nm

Side 2

Family construction form	M12
Tightening torque	0,6 Nm

Commercial data

URL Webshop	https://shop.murrelektronik.com/7000-41321-0000000
customs tariff number	85366990
EAN	4048879144681
Packaging unit	1

Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	18 V
Operating voltage DC max.	30 V
Current operating per contact max.	4 A

Diagnostics

Status indication LED	green, yellow
-----------------------	---------------

Installation | Connection

Mounting set	M3x31
--------------	-------

Installation | Pin assignment

No. of poles	PE
--------------	----

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
Additional condition protection degree	inserted, screwed
Rated surge voltage	0,8 kV
Material group (IEC 60664-1)	I

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	85 °C

Important installation notes

The information in this Product-PDF has been compiled with the utmost care.
 Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-12-01

Murrelektronik GmbH | Grabenstraße 29 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

Note on bending radius

Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.

Note on strain relief

Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.