

**MSUD double valve B-10mm with cable**

PUR 4x0.75 gy UL/CSA 7.5m

Form B (10 mm)

24 V AC  $\pm 20\%$  / DC  $\pm 25\%$ 




LED and suppression

Connection cable L = 150 mm

Further cable lengths on request.

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

**Link do produto****Ilustração**

Produto pode diferir da imagem



Cable length 7,5 m

**Side 1**

Tightening torque 0,4 Nm

|                                                 |                                                                                                                                                       |
|-------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| Thread                                          | M3                                                                                                                                                    |
| Material                                        | PBT                                                                                                                                                   |
| <b>Side 2</b>                                   |                                                                                                                                                       |
| Tightening torque                               | 0,4 Nm                                                                                                                                                |
| Thread                                          | M3                                                                                                                                                    |
| Material                                        | PBT                                                                                                                                                   |
| <b>Dados comerciais</b>                         |                                                                                                                                                       |
| ECLASS-6.0                                      | 27061801                                                                                                                                              |
| Classificação fiscal                            | 85444290                                                                                                                                              |
| GTIN                                            | 4065909098837                                                                                                                                         |
| Quantidade por embalagem                        | 1                                                                                                                                                     |
| <b>Electrical data</b>                          |                                                                                                                                                       |
| Drop-out delay time max.                        | 20 ms                                                                                                                                                 |
| <b>Electrical data   Supply</b>                 |                                                                                                                                                       |
| Operating voltage AC                            | 24 V                                                                                                                                                  |
| Operating voltage AC min.                       | 19,2 V                                                                                                                                                |
| Operating voltage AC max.                       | 28,8 V                                                                                                                                                |
| Operating voltage DC                            | 24 V                                                                                                                                                  |
| Operating voltage DC min.                       | 18 V                                                                                                                                                  |
| Operating voltage DC max.                       | 30 V                                                                                                                                                  |
| Cut-off peak voltage max.                       | 55 V                                                                                                                                                  |
| Current operating per contact max.              | 4 A                                                                                                                                                   |
| Current consumption max.                        | 12 mA                                                                                                                                                 |
| <b>Diagnostics</b>                              |                                                                                                                                                       |
| Status indication LED                           | yellow                                                                                                                                                |
| <b>Device protection   Electrical</b>           |                                                                                                                                                       |
| Degree of protection (EN IEC 60529)             | IP67                                                                                                                                                  |
| Additional condition protection degree          | inserted, screwed                                                                                                                                     |
| Rated surge voltage                             | 0,8 kV                                                                                                                                                |
| <b>Mechanical data   Material data</b>          |                                                                                                                                                       |
| Color housing                                   | black                                                                                                                                                 |
| <b>Mechanical data   Mounting data</b>          |                                                                                                                                                       |
| Mounting method                                 | inserted, screwed                                                                                                                                     |
| <b>Environmental characteristics   Climatic</b> |                                                                                                                                                       |
| Operating temperature min.                      | -25 °C                                                                                                                                                |
| Operating temperature max.                      | 85 °C                                                                                                                                                 |
| Additional condition temperature range          | depending on cable quality                                                                                                                            |
| <b>Important installation notes</b>             |                                                                                                                                                       |
| Note on strain relief                           | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.                                                   |
| Note on bending radius                          | <b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |
| <b>Installation   Cable</b>                     |                                                                                                                                                       |
| wire arrangement                                | black 1, black 2, black 3, green-yellow                                                                                                               |
| Cable identification                            | 227                                                                                                                                                   |
| Cable Type                                      | 2                                                                                                                                                     |
| Printing color of wire insulation               | white (isolation black)                                                                                                                               |
| Jacket Color                                    | gray                                                                                                                                                  |
| Type of Certificate                             | cURus                                                                                                                                                 |
| Amount stranding                                | 1                                                                                                                                                     |
| Stranding                                       | 4 wires twisted                                                                                                                                       |

|                                          |                                                  |
|------------------------------------------|--------------------------------------------------|
| wire arrangement                         | black 1, black 2, black 3, green-yellow          |
| Cable weight                             | 74,8 g/m                                         |
| Material jacket                          | PUR                                              |
| Shore hardness jacket                    | 85 ± 5 Shore A                                   |
| Freedom from ingredients (jacket)        | lead-free, cadmium-free, CFC-free, silicone-free |
| Outer-diameter (jacket)                  | 7 mm                                             |
| Tolerance outer diameter (sheath)        | ± 5 %                                            |
| Material inner jacket                    | PVC                                              |
| Color (inner jacket)                     | yellow                                           |
| Material wire insulation                 | PVC                                              |
| Amount wires                             | 4                                                |
| Outer diameter insulation                | 1,8 mm                                           |
| Outer diameter tolerance core insulation | ± 5 %                                            |
| Shore hardness wire insulation           | 43 ± 5 Shore D                                   |
| Ingredient freeness wire insulation      | lead-free, cadmium-free, CFC-free, silicone-free |
| Printing color of wire insulation        | white (isolation black)                          |
| Amount strands (wire)                    | 42                                               |
| Diameter of single wires                 | 0,15 mm                                          |
| Conductor crosssection (wire)            | 0,75 mm²                                         |
| Material conductor wire                  | Stranded copper wire, bare                       |
| Conductor type (wire)                    | strand class 6                                   |
| Electrical function wire                 | Signal                                           |
| Nominal voltage AC max.                  | 300 V                                            |
| Current load capacity (standard)         | to DIN VDE 0298-4                                |
| Current load capacity min. wire          | 9,6 A                                            |
| Electrical function wire                 | Signal                                           |
| Electrical resistance line constant wire | 26 Ω/km @ 20 °C                                  |
| Min. operating temperature (static)      | -30 °C                                           |
| Max. operating temperature (fixed)       | 80 °C                                            |
| Operating temperature min. (dynamic)     | -5 °C                                            |
| Operating temperature max. (dynamic)     | 80 °C                                            |
| chemical resistance                      | Good, application-related testing                |
| Gasoline resistance                      | Good, application-related testing                |
| Oil resistance                           | DIN EN 60811-404                                 |
| Bending radius (fixed)                   | 10 x Outer diameter                              |
| Bending radius (dynamic)                 | 15 x Outer diameter                              |
| No. of bending cycles (C-track)          | 2 Mio. @ 25 °C                                   |
| Traversing distance (C-track)            | 5 m @ 25 °C   horizontal                         |
| Travel speed (C-track)                   | 3,3 m/s @ 25 °C                                  |