


A16 Hood, high profile, IP65

Single locking lever, side entry M25

A16  
Hood (high)  
Single locking lever  
IP65  
Technical data will be only guaranteed with Murrelektronik components.

Link to Product

Illustration



Product may differ from Image

| Commercial data                        |                                         |
|----------------------------------------|-----------------------------------------|
| ECLASS-6.0                             | 27143424                                |
| ECLASS-6.1                             | 27261203                                |
| ECLASS-7.0                             | 27440202                                |
| ECLASS-8.0                             | 27440202                                |
| ECLASS-9.0                             | 27440202                                |
| ECLASS-10.1                            | 27440202                                |
| ECLASS-11.1                            | 27440202                                |
| ECLASS-12.0                            | 27440202                                |
| ETIM-5.0                               | EC000437                                |
| customs tariff number                  | 85389099                                |
| GTIN                                   | 4048879644037                           |
| Packaging unit                         | 1                                       |
| Installation                           |                                         |
| Cable outlet                           | laterally                               |
| Installation   Connection              |                                         |
| Mounting set                           | M25                                     |
| Mating cycles min.                     | 500                                     |
| Device protection   Electrical         |                                         |
| Degree of protection (EN IEC 60529)    | IP65                                    |
| Additional condition protection degree | inserted, locked, with screw connection |
| Mechanical data                        |                                         |
| Housing type                           | Hood                                    |
| Mechanical data   Material data        |                                         |

|                 |               |
|-----------------|---------------|
| Coating housing | powder-coated |
|-----------------|---------------|

|                 |          |
|-----------------|----------|
| Coating locking | verzinkt |
|-----------------|----------|

|                 |    |
|-----------------|----|
| Material gasket | CR |
|-----------------|----|

|                  |                      |
|------------------|----------------------|
| Material housing | Aluminum die casting |
|------------------|----------------------|

|                  |       |
|------------------|-------|
| Locking material | Steel |
|------------------|-------|

**Mechanical data | Mounting data**

|      |     |
|------|-----|
| Size | A16 |
|------|-----|

|        |         |
|--------|---------|
| Height | 70,5 mm |
|--------|---------|

|       |       |
|-------|-------|
| Width | 32 mm |
|-------|-------|

|       |       |
|-------|-------|
| Depth | 79 mm |
|-------|-------|

|                    |                      |
|--------------------|----------------------|
| Looking techniques | Single locking lever |
|--------------------|----------------------|

**Environmental characteristics | Climatic**

|                            |        |
|----------------------------|--------|
| Operating temperature min. | -40 °C |
|----------------------------|--------|

|                            |        |
|----------------------------|--------|
| Operating temperature max. | 100 °C |
|----------------------------|--------|

|                                    |           |
|------------------------------------|-----------|
| Climatic category (EN IEC 60068-1) | 40/100/21 |
|------------------------------------|-----------|