




MIRO 6.2 OPTO-COUPLER MODULE

IN: 30 VDC - OUT: 48 VDC / 1 A

Transistor 1 A
24 V DC
Screw terminals

[Link to Product](#)**Illustration**



Product may differ from Image

General data

Test isolation voltage	500 V
Mounting method	DIN-rail mountable (EN 60715)
Housing	Black plastic, flame retardant
Temperature range	-20...+60 °C
Dimensions H×W×D	78×6.2×70 mm

Output

Switching voltage	3...48 V DC
Switching current per output	500 µA...1 A
Saturation voltage (across output)	max. 0.12 V DC
Leakage current (output is open)	max. 25 µA
Switching time ON/OFF	1.5/1 ms (100 mA load)
Switching frequency	max. 40/4 Hz (resist./ind.)

Input

Voltage range ON	11...30 V DC
Voltage range OFF	0...5 V DC
Control current	6 mA
LED display	LED (yellow)

Commercial data

country of origin	CZ
customs tariff number	85414090
EAN	4048879026826
eClass	27371604
Packaging unit	1