

MVP12-V, 8XM12, 4POLE, M23 12POL. CON.

Connector exit frontside

8-way, 4-pole


M23 plug connection

12-pole used


with LED for digital PNP-signals 24 V DC

Plastic housings with good resistance against chemicals and oils.



The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**


M12-Females 4-pole





M23-Plug



for 1 signal per port





Product may differ from Image

Approvals



Technical Data

Operating voltage	24 V DC
Operating current per contact	max. 4 A
Signal per port	1 - (31-32)
Total current	max. 10 A
Housing	Plastic, flame retardant
Protection	IP67 inserted and tightened (EN 60529)
Locking of ports	Screw thread (M12×1 mm)

General data

Temperature range	-20...+80 °C
Dimensions H×W×D	149.2×50.2×16.5 mm

Contact Layout

PIN 1	(+)
PIN 3	(-)
PIN 4	(NO)/(S1)
PIN 5	(Earth)
LED (green): Power / LED (yellow): (S1)	

Commercial data

country of origin	DE
customs tariff number	85369010
EAN	4048879063371
eClass	27279219
Packaging unit	1