MURR ELEKTRONIK
stay connected

AMS 4-10/44-2 OPTO-COUPLER MODULE


In: 24 VDC - Out: 24 VDC / 2A


Transistor 2 A (4-way)
4 NO contacts
24 V DC

[Link to Product]

Illustration







Product may differ from Image

Commercial data

ECLASS-6.0	27371604
ECLASS-6.1	27371604
ECLASS-7.0	27371604
ECLASS-8.0	27371604
ECLASS-9.0	27371604
ECLASS-10.1	27371604

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28

MURR ELEKTRONIK
stay connected

ECLASS-11.1	27371604
ECLASS-12.0	27371604
ETIM-5.0	EC001504
customs tariff number	85414900
GTIN	4048879295451
Packaging unit	1
Electrical data | Input	
Input voltage OFF DC min.	0 V
Input voltage OFF DC max.	6 V
Input voltage DC min.	20 V
Input voltage DC max.	30 V
Input current	27 mA
Electrical data | Output	
Switch off delay max.	5 ms
Switch on delay max.	1 ms
Quiescent current OFF max.	0,01 mA
Switching frequency inductive max.	1 Hz
Switching frequency ohmic max.	10 Hz
Voltage switching DC min.	5 V
Switching voltage DC max.	30 V
Switching current min.	1 mA
Switching current max.	2 A
Voltage drop DC max.	0,05 V
Diagnostics	
Status indication LED	yellow
Device protection | Electrical	
Rated surge voltage	2,5 kV
Device protection | Media	
Flame resistance	flame retardant
Mechanical data | Material data	
Color housing	black
Material housing	Plastic
Mechanical data | Mounting data	
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, G32, (EN 60715)
Height	75 mm
Width	22,5 mm
Depth	102 mm
Environmental characteristics | Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	50 °C

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28