MURR ELEKTRONIK
stay connected

CAN-PLUG-MALE (SUB-D) 90°

Screw terminals up to 1Mbits/s

Bus connection plug 90°
SUB-D9 (female), screw terminals
max. 1 Mbit/s with switchable terminal resistors
CANopen
Plastic housings with good resistance against chemicals and oils.
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration



Product may differ from Image

Commercial data	
ECLASS-6.0	27279221
ECLASS-7.0	27440104
ECLASS-8.0	27440104
ECLASS-9.0	27440102
ECLASS-10.1	27242692
ECLASS-11.1	27242692
ECLASS-12.0	27242692
ETIM-5.0	EC002584
customs tariff number	85366990
GTIN	4048879049825
Packaging unit	1
Electrical data	
Terminating resistor	connectable, integrated
Industrial communication	
Data transmission rate max.	1 MBit/s
Installation	
Connection cross section max.	1 mm²
Device protection | Electrical	
Degree of protection (EN IEC 60529)	IP20
Mechanical data | Mounting data	
Height	65 mm

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29

Width	48 mm
Depth	16 mm
Environmental characteristics | Climatic	
Operating temperature min.	0 °C
Operating temperature max.	60 °C
Storage temperature min.	-25 °C
Storage temperature max.	80 °C
Connection type 2	
Family construction form	D-Sub
Gender	female
No. of poles	9
PIN 2	CAN_L
PIN 3	CAN_GND
PIN 5	CAN_SHLD
PIN 6	0 V
PIN 7	CAN_H
PIN 9	CAN V +
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
No. of poles	6

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29