

SLIM LINE POTENTIAL TERMINAL BLOCK


Potential terminal block  
Slim Line

[Link to Product](#)

Illustration



Product may differ from Image



| Commercial data                          |               |
|------------------------------------------|---------------|
| ECLASS-6.0                               | 27141106      |
| ECLASS-6.1                               | 27141106      |
| ECLASS-7.0                               | 27141106      |
| ECLASS-8.0                               | 27141106      |
| ECLASS-9.0                               | 27141106      |
| ECLASS-10.1                              | 27141106      |
| ECLASS-11.1                              | 27141106      |
| ECLASS-12.0                              | 27141106      |
| ETIM-5.0                                 | EC001283      |
| customs tariff number                    | 85369010      |
| GTIN                                     | 4048879049429 |
| Packaging unit                           | 1             |
| Electrical data   Supply                 |               |
| Operating voltage AC max.                | 30 V          |
| Operating voltage DC max.                | 30 V          |
| Total current max.                       | 20 A          |
| Device protection   Electrical           |               |
| Degree of protection (EN IEC 60529)      | IP20          |
| Mechanical data   Mounting data          |               |
| Height                                   | 70 mm         |
| Width                                    | 56 mm         |
| Depth                                    | 32,5 mm       |
| Environmental characteristics   Climatic |               |

|                            |      |
|----------------------------|------|
| Operating temperature min. | 0 °C |
|----------------------------|------|

|                            |       |
|----------------------------|-------|
| Operating temperature max. | 55 °C |
|----------------------------|-------|

|                          |        |
|--------------------------|--------|
| Storage temperature min. | -40 °C |
|--------------------------|--------|

|                          |       |
|--------------------------|-------|
| Storage temperature max. | 85 °C |
|--------------------------|-------|

#### Connection type 4

|            |                           |
|------------|---------------------------|
| Connection | Spring clamp terminals FK |
|------------|---------------------------|

|                          |          |
|--------------------------|----------|
| Family construction form | terminal |
|--------------------------|----------|

|        |        |
|--------|--------|
| Gender | female |
|--------|--------|

|                       |       |
|-----------------------|-------|
| Color contact carrier | green |
|-----------------------|-------|

|              |   |
|--------------|---|
| No. of poles | 1 |
|--------------|---|

|       |    |
|-------|----|
| PIN 1 | 00 |
|-------|----|

|            |                           |
|------------|---------------------------|
| Connection | Spring clamp terminals FK |
|------------|---------------------------|

|                          |          |
|--------------------------|----------|
| Family construction form | terminal |
|--------------------------|----------|

|        |        |
|--------|--------|
| Gender | female |
|--------|--------|

|                       |       |
|-----------------------|-------|
| Color contact carrier | green |
|-----------------------|-------|

|              |   |
|--------------|---|
| No. of poles | 1 |
|--------------|---|

|       |    |
|-------|----|
| PIN 1 | 01 |
|-------|----|

|            |                           |
|------------|---------------------------|
| Connection | Spring clamp terminals FK |
|------------|---------------------------|

|                          |          |
|--------------------------|----------|
| Family construction form | terminal |
|--------------------------|----------|

|        |        |
|--------|--------|
| Gender | female |
|--------|--------|

|                       |       |
|-----------------------|-------|
| Color contact carrier | black |
|-----------------------|-------|

|              |   |
|--------------|---|
| No. of poles | 7 |
|--------------|---|

|       |    |
|-------|----|
| PIN 1 | 00 |
|-------|----|

|       |    |
|-------|----|
| PIN 2 | 01 |
|-------|----|

|       |    |
|-------|----|
| PIN 3 | 02 |
|-------|----|

|       |    |
|-------|----|
| PIN 4 | 03 |
|-------|----|

|       |    |
|-------|----|
| PIN 5 | 04 |
|-------|----|

|       |    |
|-------|----|
| PIN 6 | 05 |
|-------|----|

|       |    |
|-------|----|
| PIN 7 | 06 |
|-------|----|

|            |                           |
|------------|---------------------------|
| Connection | Spring clamp terminals FK |
|------------|---------------------------|

|                          |          |
|--------------------------|----------|
| Family construction form | terminal |
|--------------------------|----------|

|        |        |
|--------|--------|
| Gender | female |
|--------|--------|

|                       |       |
|-----------------------|-------|
| Color contact carrier | black |
|-----------------------|-------|

|              |   |
|--------------|---|
| No. of poles | 7 |
|--------------|---|

|       |    |
|-------|----|
| PIN 1 | 07 |
|-------|----|

|       |    |
|-------|----|
| PIN 2 | 08 |
|-------|----|

|       |    |
|-------|----|
| PIN 3 | 09 |
|-------|----|

|       |    |
|-------|----|
| PIN 4 | 10 |
|-------|----|

|       |    |
|-------|----|
| PIN 5 | 11 |
|-------|----|

|       |    |
|-------|----|
| PIN 6 | 12 |
|-------|----|

|       |    |
|-------|----|
| PIN 7 | 13 |
|-------|----|