

CUBE67 BUS NODES

CANopen

CANopen
Connection cables are in the online shop under "Connection Technology".
Housing fully potted.

Link to Product

Illustration



Product may differ from Image



| Commercial data | |
|-------------------------------------|---------------|
| ECLASS-6.0 | 27242608 |
| ECLASS-6.1 | 27242608 |
| ECLASS-7.0 | 27242608 |
| ECLASS-8.0 | 27242608 |
| ECLASS-9.0 | 27242608 |
| ECLASS-10.1 | 27242608 |
| ECLASS-11.1 | 27242608 |
| ECLASS-12.0 | 27242608 |
| ETIM-5.0 | EC001604 |
| customs tariff number | 85389099 |
| GTIN | 4048879048712 |
| Packaging unit | 1 |
| Electrical data Supply | |
| Operating voltage DC | 24 V |
| Current consumption max. | 70 mA |
| Total current UA max. | 9 A |
| Total current US max. | 9 A |
| Industrial communication Bus data | |
| Address range min. | 1 |
| Address range max. | 99 |
| Industrial communication CANopen | |

CANopen addressing

Rotary switch

Diagnostics

| | |
|-------------------------|----------------------------------|
| Diagnostic | No voltage, Under voltage |
| Diagnostic via BUS | per module and channel |
| Diagnostic via LED | per module and channel |
| Short circuit diagnosis | yes |
| LED display | Ethernet connection/data traffic |
| Overload diagnosis | yes |

Device protection | Electrical

| | |
|-------------------------------------|------|
| Degree of protection (EN IEC 60529) | IP67 |
|-------------------------------------|------|

Mechanical data

| | |
|-------------------------------|----|
| Number extension modules max. | 16 |
|-------------------------------|----|

Mechanical data | Mounting data

| | |
|----------------------------|-----------------------|
| Suitable for mounting type | 2-hole screw mounting |
| Height | 151 mm |
| Width | 50 mm |
| Depth | 50,3 mm |

Environmental characteristics | Climatic

| | |
|----------------------------|--------|
| Operating temperature min. | 0 °C |
| Operating temperature max. | 55 °C |
| Storage temperature min. | -20 °C |
| Storage temperature max. | 75 °C |

Conformity

| | |
|------------------|------------|
| Product standard | EN 61131-2 |
|------------------|------------|

Connection type 4

| | |
|--------------------------|----------------------------|
| Connection type 1 | Bus In |
| Connection type 2 | Bus Out |
| Connection type 3 | Internal system connection |
| Connection type 4 | Power |
| Family construction form | M12 |
| Gender | male |
| Color contact carrier | black |
| Coding | A |
| No. of poles | 5 |
| PIN 1 | Shield |
| PIN 2 | n.c. |
| PIN 3 | 0 V |
| PIN 4 | CAN_HIGH |
| PIN 5 | CAN_LOW |
| Family construction form | M12 |
| Gender | female |
| Color contact carrier | black |
| Coding | A |
| No. of poles | 5 |
| PIN 1 | Shield |
| PIN 2 | n.c. |
| PIN 3 | 0 V |
| PIN 4 | CAN_HIGH |
| PIN 5 | CAN_LOW |
| Family construction form | M12 |
| Gender | female |

| | |
|--------------------------|--------------|
| Color contact carrier | black |
| Coding | A |
| No. of poles | 6 |
| PIN 1 | 24 V DC (UA) |
| PIN 2 | 24 V DC (US) |
| PIN 3 | 0 V |
| PIN 4 | Bus internal |
| PIN 5 | Bus internal |
| PIN 6 | 0 V |
| Family construction form | 7/8" |
| Gender | male |
| Color contact carrier | black |
| No. of poles | 5 |
| PIN 1 | 0 V |
| PIN 2 | 0 V |
| PIN 3 | PE |
| PIN 4 | 24 V DC (US) |
| PIN 5 | 24 V DC (UA) |