MURR ELEKTRONIK
stay connected

## MASI67 INSTALLATION TECHNOLOGY


Converter 2x profile cable to 7/8" male


MASI67 converter
2× profile cable to 7/8" (male)
Connection cables are in the online shop under "Connection Technology".

Link to Product

### Illustration






Product may differ from Image

### Commercial data

| | |
|---|---|
| ECLASS-6.0 | 27400209 |
| ECLASS-6.1 | 27279219 |
| ECLASS-7.0 | 27279219 |
| ECLASS-8.0 | 27279219 |
| ECLASS-9.0 | 27440108 |
| ECLASS-10.1 | 27440111 |

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29

MURR ELEKTRONIK
stay connected

| | |
|---|---|
| ECLASS-11.1 | 27440111 |
| ECLASS-12.0 | 27440111 |
| ETIM-5.0 | EC001583 |
| customs tariff number | 85369010 |
| GTIN | 4048879052153 |
| Packaging unit | 1 |
| **Electrical data \| Supply** | |
| Operating voltage DC max. | 36 V |
| Total current max. | 8 A |
| **Device protection \| Electrical** | |
| Degree of protection (EN IEC 60529) | IP67 |
| Insulation strength ASI/Power | 200 V |
| **Mechanical data \| Mounting data** | |
| Mounting method | screwed, geschnappt |
| Suitable for mounting type | mounting rail, (EN 60715) |
| Height | 90 mm |
| Width | 74 mm |
| Depth | 46 mm |
| **Environmental characteristics \| Climatic** | |
| Operating temperature min. | -20 °C |
| Operating temperature max. | 60 °C |
| Storage temperature min. | -40 °C |
| Storage temperature max. | 80 °C |
| **Conformity** | |
| Product standard | EN 60664-1 |
| **Connection type 1** | |
| Family construction form | 7/8" |
| Gender | male |
| Color contact carrier | black |
| No. of poles | 5 |
| PIN 1 | AS-i + |
| PIN 2 | AS-i - |
| PIN 3 | n.c. |
| PIN 4 | 24 V DC |
| PIN 5 | 0 V |

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29