MURR ELEKTRONIK
stay connected


## CUBE67 I/O EXTENSION MODULE


4 analog inputs (RTD)

Expansion module
AI4 - (E) 4× M12 (RTD)
for resistors and temperature
Connection cables are in the online shop under "Connection Technology".
Housing fully potted.

**Link to Product**

### Illustration






Product may differ from Image

### Commercial data

| | |
|---|---|
| ECLASS-6.0 | 27242601 |
| ECLASS-6.1 | 27242601 |
| ECLASS-7.0 | 27242601 |
| ECLASS-8.0 | 27242601 |
| ECLASS-9.0 | 27242601 |
| ECLASS-10.1 | 27242601 |
| ECLASS-11.1 | 27242601 |
| ECLASS-12.0 | 27242601 |
| ETIM-5.0 | EC001596 |
| customs tariff number | 85389099 |
| GTIN | 4048879048200 |
| Packaging unit | 1 |

### Electrical data | Supply

| | |
|---|---|
| Current consumption max. | 50 mA |
| Total current UA max. | 4 A |
| Total current US max. | 4 A |

### Electrical data | Input

| | |
|---|---|
| Sensor type | Pt100, Pt200, Pt500, Pt1000, Ni100, Ni120, Ni200, Ni500, Ni1000, 0...3000 Ohm, R |
| Conversion time analog input per channel | 58 ms |

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28

MURR ELEKTRONIK
stay connected

| | |
|---|---|
| **Diagnostics** | |
| Actuator warning | per channel via LED and BUS |
| Diagnostic | No voltage, Under voltage |
| Diagnostic via BUS | per module and channel |
| Diagnostic via LED | per module and channel |
| Short circuit diagnosis | yes |
| LED display | Ethernet connection/data traffic |
| Overload diagnosis | yes |
| **Device protection \| Electrical** | |
| Degree of protection (EN IEC 60529) | IP67 |
| **Mechanical data \| Mounting data** | |
| Suitable for mounting type | 2-hole screw mounting |
| Height | 150 mm |
| Width | 30 mm |
| Depth | 34,5 mm |
| **Environmental characteristics \| Climatic** | |
| Operating temperature min. | 0 °C |
| Operating temperature max. | 55 °C |
| Storage temperature min. | -20 °C |
| Storage temperature max. | 75 °C |
| **Connection type 3** | |
| Connection type 1 | 0-3 |
| Connection type 2 | Bus In |
| Connection type 3 | Bus Out |
| Family construction form | M12 |
| Gender | female |
| Color contact carrier | black |
| Coding | A |
| No. of poles | 5 |
| PIN 1 | RD |
| PIN 2 | RD |
| PIN 3 | WH |
| PIN 4 | WH |
| PIN 5 | n.c. |
| Family construction form | M12 |
| Gender | male |
| Color contact carrier | black |
| Coding | A |
| No. of poles | 6 |
| PIN 1 | 24 V DC (UA) |
| PIN 2 | 24 V DC (US) |
| PIN 3 | 0 V |
| PIN 4 | Bus internal |
| PIN 5 | Bus internal |
| PIN 6 | 0 V |
| Family construction form | M12 |
| Gender | female |
| Color contact carrier | black |
| Coding | A |
| No. of poles | 6 |
| PIN 1 | 24 V DC (UA) |
| PIN 2 | 24 V DC (US) |

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28

| | |
|---|---|
| PIN 3 | 0 V |
| PIN 4 | Bus internal |
| PIN 5 | Bus internal |
| PIN 6 | 0 V |

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28