MURR ELEKTRONIK
stay connected

10 Port unmanaged Gigabit Switch 4 PoE 2 SFP Ports IP20 metal

10 Port Unmanaged IP20 PoE Gigabit Switch Metal
24 V power supply
4 PoE ports – 2 SFP ports

Link to Product

Illustration



Product may differ from Image

Commercial data

ECLASS-6.1	19170106
ECLASS-7.0	19170106
ECLASS-8.0	19170106
ECLASS-9.0	19170402
ECLASS-10.1	19170402
ECLASS-11.1	19170402
ECLASS-12.0	19170402
customs tariff number	85176200
GTIN	4048879844215
Packaging unit	1

Electrical data | Supply

Operating voltage DC min.	12 V
Operating voltage DC max.	57 V
PoE voltage amplifier	yes

Industrial communication

Data transmission rate max.	1000 MBit/s

Industrial communication | Ethernet functionality

Auto-crossover	yes
Auto-negotiation	yes
duplex	Full duplex
Switch type	unmanaged
VLAN unmanaged (IEEE 802.1Q)	yes

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29

Murrelektronik GmbH | Falkenstraße 3 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

MURR ELEKTRONIK
stay connected

Diagnostics	
Alarm contact	yes
Diagnostic	No voltage
LED display	Ethernet connection/data traffic
Device protection | Electrical	
Degree of protection (EN IEC 60529)	IP20
Mechanical data | Material data	
Color housing	black
Material housing	Metal
Mechanical data | Mounting data	
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)
Height	145 mm
Width	57,8 mm
Depth	113 mm
Environmental characteristics | Climatic	
Operating temperature min.	-40 °C
Operating temperature max.	70 °C
Storage temperature min.	-40 °C
Storage temperature max.	85 °C
Connection type 3	
Connection type 1	8
Connection type 2	10
Connection type 3	X1
Family construction form	RJ45
Gender	female
Color contact carrier	black
No. of poles	8
PIN 1	TD +
PIN 2	TD -
PIN 3	RD +
PIN 4	n.c.
PIN 5	n.c.
PIN 6	RD -
PIN 7	n.c.
PIN 8	n.c.
Family construction form	POF SC-RJ
Gender	female
Color contact carrier	black
No. of poles	2
PIN 1	RD
PIN 2	TD
Connection	Plug-in terminals RK
Family construction form	terminal
Gender	male
Color contact carrier	green
No. of poles	7
PIN 1	FE
PIN 2	V 1 -
PIN 3	V 1 +
PIN 4	Relay (NO)
PIN 5	Relay (NO)

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29

PIN 6	V 2 -
PIN 7	V 2 +

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29