MURR ELEKTRONIK
stay connected

MB CAP ULTRA ADD-ON-MODULE


IN: 0-26,4VDC OUT:0-26,4VDC/3A for max.1A/21S


INPUT: 24 V DC (SELV/PELV)
OUTPUT: max. 3 A
12 s (3 A); 36 s (1 A)

[Link to Product]

Illustration







Product may differ from Image

Commercial data

ECLASS-6.0	27049190
ECLASS-6.1	27049201
ECLASS-7.0	27049201
ECLASS-8.0	27049201
ECLASS-9.0	27049201
ECLASS-10.1	27040692

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29

MURR ELEKTRONIK
stay connected

ECLASS-11.1	27040692
ECLASS-12.0	27040692
ETIM-5.0	EC002584
customs tariff number	85322900
GTIN	4048879079792
Packaging unit	1
Electrical data	
Security level	SELV/PELV
Electrical data | Input	
Input voltage DC min.	0 V
Input voltage DC max.	26,4 V
Current input AC	3 A
Efficiency	90 %
Electrical data | Output	
Output voltage DC min.	0 V
Output voltage DC max.	26,4 V
Output voltage adjustable	yes
Output current max.	3 A
Mechanical data | Mounting data	
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)
Environmental characteristics | Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	60 °C
Storage temperature min.	-20 °C
Storage temperature max.	60 °C
Conformity	
Product standard	EN 60950, EN 50178

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29