MURR ELEKTRONIK
stay connected

MPL POWER SUPPLY 3-PHASE, SMOOTHED


IN: 208-520VAC+/- 5% OUT: 24V/25ADC


Current: 25 A
Output rating: 600 W
This power supply units meet the (EN 61000-3-2) standard for harmonic current.
Any mounting position on vertical wall, condensation not permissible

Link to Product

Illustration







Product may differ from Image

Commercial data

ECLASS-6.0	27049002
ECLASS-6.1	27049002
ECLASS-7.0	27049002
ECLASS-8.0	27049002
ECLASS-9.0	27040701
ECLASS-10.1	27040701

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29

MURR ELEKTRONIK
stay connected

ECLASS-11.1	27040701
ECLASS-12.0	27040701
ETIM-5.0	EC002540
customs tariff number	85044095
GTIN	4048879079105
Packaging unit	1
Electrical data	
Security level	SELV
Electrical data | Supply	
Power frequency	50 ... 60 Hz
Electrical data | Input	
Input voltage AC min.	208 V
Input voltage AC max.	520 V
Phase number input	3
Efficiency	73 %
Electrical data | Output	
Fuse protection secondary side external	25 A
Output suppression	LED, Screening capacitor, VDR
Output voltage DC	24 V
Output voltage adjustable	no
Output current max.	25 A
Characteristic secondary fuse	Inertia
Ripple max.	2 %
Mechanical data | Mounting data	
Suitable for mounting type	Schlüssellochaufhängung
Mounting dimension a	195 mm
Mounting dimension b	79,5 mm
Mounting dimension c	6,5 mm
Height	220 mm
Width	101,5 mm
Depth	213 mm
Environmental characteristics | Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	55 °C
Conformity	
Product standard	EN 61558-2-6, EN 62041 category I
EMC	EN 55011 B, EN 61000-3-2

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29