MURR ELEKTRONIK
stay connected

MST 1-PHASE CONTROL AND ISOLATION TRANSFORMER


P: 4000VA IN: 208...550VAC OUT: 2x115VAC


Single-phase - Control and Isolation Transformers
4000 VA
Isolation class T 40/B
Other voltages on request.

Link to Product

Illustration







Product may differ from Image

Commercial data

ECLASS-6.0	27031302
ECLASS-6.1	27031302
ECLASS-7.0	27031302
ECLASS-8.0	27031302
ECLASS-9.0	27031302
ECLASS-10.1	27031302

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28

MURR ELEKTRONIK
stay connected

ECLASS-11.1	27031302
ECLASS-12.0	27031302
ETIM-5.0	EC002486
customs tariff number	85043200
GTIN	4048879375542
Packaging unit	1
Electrical data | Supply	
Power frequency	50 ... 60 Hz
Electrical data | Input	
Input voltage 1 AC	208 V
Input voltage 2 AC	550 V
Input voltage AC	208, 230, 380, 400, 420, 440, 460, 480, 500, 525, 550
Input current at input voltage 1 AC	20 A
Input current at input voltage 2 AC	7,7 A
Inrush current at input voltage 1	372 A
Inrush current at input voltage 2	141 A
Short-circuit current at input voltage 1	960 A
Short-circuit current at input voltage 2	367 A
Electrical data | Output	
Output voltage	1 × 230 / 1 × 115 / 2 × 115 V AC
Output voltage AC 1	230 V
Output voltage AC 2	115 V
Output voltage adjustable	yes
Power rating AC max.	4000 VA
Device protection | Electrical	
Insulation test voltage input - output	4 kV
Mechanical data | Mounting data	
Suitable for mounting type	Long-hole mounting
Mounting dimension a	200 mm
Mounting dimension b	174 mm
Mounting dimension c	9 mm
Height	213 mm
Width	197 mm
Depth	250 mm
Diameter bore	9 mm
Length bore	14 mm
Environmental characteristics | Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	40 °C
Storage temperature min.	-40 °C
Storage temperature max.	80 °C
Conformity	
Product standard	EN 61558-1, EN 61558-2-4, EN 62041 category 0

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28