MURR ELEKTRONIK
stay connected

MDD DC/DC-CONVERTOR SWITCH MODE


IN: 24VDC OUT: 5V/1,5ADC


INPUT: 24 V DC
OUTPUT: 5 V DC
Output rating: 7.5 W
Current: 1.5 A
Condensation not permitted
Restart after overload by removing supply voltage

Link to Product

Illustration







Product may differ from Image

Commercial data

ECLASS-6.0	27210901
ECLASS-6.1	27210901
ECLASS-7.0	27210901
ECLASS-8.0	27210901

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29

MURR ELEKTRONIK
stay connected

ECLASS-9.0	27210901
ECLASS-10.1	27210901
ECLASS-11.1	27210901
ECLASS-12.0	27210901
ETIM-5.0	EC002540
customs tariff number	85043121
GTIN	4048879079532
Packaging unit	1
Electrical data	
Security level	SELV
Electrical data | Input	
Fuse protection primary side internal	1,5 A
Characteristic back-up fuse	Inertia
Input voltage DC	24 V
Current input AC	0,6 A
Electrical data | Output	
Output voltage DC	5 V
Output voltage DC min.	4,9 V
Output voltage DC max.	5,1 V
Output voltage adjustable	no
Output current max.	1,5 A
Ripple max.	0,2 %
Device protection | Electrical	
Insulation test voltage input - output	4 kV
Short-circuit protected	yes
Overload resistant	yes
Mechanical data | Mounting data	
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, G32, (EN 60715)
Environmental characteristics | Climatic	
Operating temperature min.	0 °C
Operating temperature max.	50 °C
Conformity	
Low Voltage Directive	EN 61204-3
Connection type 1	
Connection type 1	Output
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
No. of poles	4
PIN 1	+
PIN 2	+
PIN 3	-
PIN 4	-

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29