



Bus terminating plug M12 male B-cod.

Profibus


PROFIBUS  
Terminating resistor  
Male  
M12, 4-pole  
B-coded

Link to Product

Illustration



Product may differ from Image



| Side 1                              |         |
|-------------------------------------|---------|
| Tightening torque                   | 0,6 Nm  |
| Family construction form            | M12     |
| Thread                              | M12 x 1 |
| Degree of protection (EN IEC 60529) | IP67    |
| Commercial data                     |         |

|                                                 |                                       |
|-------------------------------------------------|---------------------------------------|
| ECLASS-6.0                                      | 19070403                              |
| ECLASS-6.1                                      | 27260702                              |
| ECLASS-7.0                                      | 27440390                              |
| ECLASS-8.0                                      | 27440190                              |
| ECLASS-9.0                                      | 27440190                              |
| ECLASS-10.1                                     | 27440190                              |
| ECLASS-11.1                                     | 27440190                              |
| ECLASS-12.0                                     | 27440190                              |
| ETIM-5.0                                        | EC001855                              |
| customs tariff number                           | 85331000                              |
| GTIN                                            | 4048879198592                         |
| Packaging unit                                  | 1                                     |
| <b>Electrical data   Supply</b>                 |                                       |
| Operating voltage DC max.                       | 30 V                                  |
| Operating voltage DC max. (UL-listed)           | 30 V                                  |
| Current operating per contact max.              | 4 A                                   |
| <b>Installation   Pin assignment</b>            |                                       |
| Coding                                          | B                                     |
| <b>Device protection   Electrical</b>           |                                       |
| Additional condition protection degree          | inserted, screwed                     |
| Pollution Degree                                | 3                                     |
| Rated surge voltage                             | 0,8 kV                                |
| Material group (IEC 60664-1)                    | I                                     |
| <b>Mechanical data   Material data</b>          |                                       |
| Coating locking                                 | Nickel                                |
| Locking material                                | Zinc die-casting                      |
| <b>Mechanical data   Mounting data</b>          |                                       |
| Mounting method                                 | inserted, screwed, Shaking protection |
| <b>Environmental characteristics   Climatic</b> |                                       |
| Operating temperature min.                      | -25 °C                                |
| Operating temperature max.                      | 85 °C                                 |