

M12-PANEL FEED THROUGH A-CODED




Control cabinet entry system


Male - female

M12, 5-pole

A-coded

shielded

[Link to Product](#)**Illustration**



Product may differ from Image



| Side 1 | |
|--|-------------------|
| Family construction form | M12 |
| Coding | A |
| Side 2 | |
| Family construction form | M12 |
| Coding | A |
| Commercial data | |
| ECLASS-6.0 | 27143423 |
| ECLASS-6.1 | 27279220 |
| ECLASS-7.0 | 27440103 |
| ECLASS-8.0 | 27440103 |
| ECLASS-9.0 | 27440109 |
| ECLASS-10.1 | 27440109 |
| ECLASS-11.1 | 27440109 |
| ECLASS-12.0 | 27440109 |
| ETIM-5.0 | EC001855 |
| customs tariff number | 85366990 |
| GTIN | 4048879143233 |
| Packaging unit | 1 |
| Electrical data Supply | |
| Operating voltage AC max. | 60 V |
| Operating voltage DC max. | 60 V |
| Operating voltage AC (UL-listed) | 30 V |
| Operating voltage DC (UL-listed) | 30 V |
| Current operating per contact max. | 4 A |
| Installation Connection | |
| Tightening torque | 0,6 Nm |
| Mounting set | M16 x 1.5 |
| Device protection Electrical | |
| Degree of protection (EN IEC 60529) | IP65, IP67 |
| Protection NEMA | 3, 4, 6P |
| Additional condition protection degree | inserted, screwed |

| | |
|---|---------------------------------------|
| Pollution Degree | 2 |
| Rated surge voltage | 1,5 kV |
| Material group (IEC 60664-1) | I |
| Mechanical data Material data | |
| Coating housing | nickel plated |
| Material housing | Brass |
| Mechanical data Mounting data | |
| Mounting method | inserted, screwed, Shaking protection |
| Environmental characteristics Climatic | |
| Operating temperature min. | -25 °C |
| Operating temperature max. | 85 °C |
| Approvals | |
| UL 50E | yes |