

Adapter M12 male/ female B-cod. / D-Sub 9-pol. 90°

Shielded, 12Mbit/s

PROFIBUS  
Bus connection plug 90°  
SUB-D9 (male); M12× 1 mm, B-coded  
Programming device

Link to Product

Illustration



Product may differ from Image



| Commercial data             |                         |
|-----------------------------|-------------------------|
| ECLASS-6.0                  | 27061801                |
| ECLASS-7.0                  | 27061801                |
| ECLASS-8.0                  | 27061801                |
| ECLASS-9.0                  | 27061801                |
| ECLASS-10.1                 | 27242692                |
| ECLASS-11.1                 | 27242692                |
| ECLASS-12.0                 | 27242692                |
| ETIM-5.0                    | EC001855                |
| customs tariff number       | 85366990                |
| GTIN                        | 4048879371360           |
| Packaging unit              | 1                       |
| Electrical data             |                         |
| Terminating resistor        | connectable, integrated |
| Electrical data   Supply    |                         |
| Operating voltage DC min.   | 4,75 V                  |
| Operating voltage DC max.   | 5,25 V                  |
| Current consumption max.    | 12,5 mA                 |
| Industrial communication    |                         |
| Data transmission rate max. | 12 MBit/s               |
| Installation   Connection   |                         |

|                          |     |
|--------------------------|-----|
| Family construction form | M12 |
|--------------------------|-----|

**Device protection | Electrical**

|                                     |      |
|-------------------------------------|------|
| Degree of protection (EN IEC 60529) | IP30 |
|-------------------------------------|------|

**Mechanical data | Mounting data**

|        |       |
|--------|-------|
| Height | 70 mm |
|--------|-------|

|       |       |
|-------|-------|
| Width | 35 mm |
|-------|-------|

|       |       |
|-------|-------|
| Depth | 17 mm |
|-------|-------|

**Environmental characteristics | Climatic**

|                            |      |
|----------------------------|------|
| Operating temperature min. | 0 °C |
|----------------------------|------|

|                            |       |
|----------------------------|-------|
| Operating temperature max. | 60 °C |
|----------------------------|-------|