

**MODL. VARIO insert for fixed housing type B**

6/4 shut-off, stainless steel type 1.4404 (V4A)

Modlink Vario  
Insert - stationary housing  
Stainless steel 1.4404 (V4A)  
with shut-off  
AD6

[Link to Product](#)

Illustration



Product may differ from Image

Commercial data

|                       |               |
|-----------------------|---------------|
| ECLASS-6.0            | 27260702      |
| ECLASS-6.1            | 27260708      |
| ECLASS-7.0            | 27440312      |
| ECLASS-8.0            | 27440312      |
| ECLASS-9.0            | 27440312      |
| ECLASS-10.1           | 27440312      |
| ECLASS-11.1           | 27440312      |
| ECLASS-12.0           | 27440312      |
| ETIM-5.0              | EC002641      |
| customs tariff number | 73269098      |
| GTIN                  | 4048879574211 |
| Packaging unit        | 1             |

Device protection | Electrical

|                                        |                   |
|----------------------------------------|-------------------|
| Degree of protection (EN IEC 60529)    | IP65, IP67, IP68  |
| Degree of protection (ISO 20653:2013)  | IP66K, IP69K      |
| Additional condition protection degree | inserted, screwed |

Mechanical data

|                         |               |
|-------------------------|---------------|
| Barrier                 | with shut-off |
| Operating pressure min. | 0 bar         |
| Operating pressure max. | 16 bar        |

Mechanical data | Material data

|                  |                              |
|------------------|------------------------------|
| Material gasket  | FPM                          |
| Material housing | Stainless steel 1.4404 (V4A) |

Mechanical data | Mounting data

|                                                 |        |
|-------------------------------------------------|--------|
| Outer diameter hose                             | 6 mm   |
| <b>Environmental characteristics   Climatic</b> |        |
| Operating temperature min.                      | -20 °C |
| Operating temperature max.                      | 120 °C |