MIRO TR 24VDC SK OPTO-COUPLER MODULE

IN: 53 VDC - OUT: 48 VDC / 0,5 A

Art.No.: 52500
Weight: 0.028 kg
Country of origin: CZ
Model designation: MIRO,TR,24VDC,SK

Transistor 0.5 A
24 V DC
Screw terminals

[Link to Product]

Illustration







Product may differ from Image

Commercial data

URL Webshop	https://shop.murrelektronik.com/52500
GTIN	4048879026949
EU-Customs tariff number	85414900
US-Customs tariff number	8541499500

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-09-14

ECLASS-6.0	27371604
ECLASS-6.1	27371604
ECLASS-7.0	27371604
ECLASS-7.1	27371604
ECLASS-8.0	27371604
ECLASS-8.1	27371604
ECLASS-9.0	27371604
ECLASS-9.1	27371604
ECLASS-10.0.1	27371604
ECLASS-10.1	27371604
ECLASS-11.0	27371604
ECLASS-11.1	27371604
ECLASS-12.0	27371604
ECLASS-13.0	27371604
ECLASS-14.0	27371604
ETIM-5.0	EC001504
ETIM-6.0	EC001504
ETIM-7.0	EC001504
ETIM-8.0	EC001504
ETIM-9.0	EC001504
ETIM-10.0	EC001504
customs tariff number	85414900
EAN	4048879026949
Packaging unit	1
Electrical data | Input	
Input voltage DC min.	10 V
Input voltage DC max.	53 V
Input voltage OFF DC min.	0 V
Input voltage OFF DC max.	5 V
Current input DC	6 mA
Electrical data | Output	
Voltage drop DC max.	1,2 V
Quiescent current OFF max.	0,01 mA
Switch on delay max.	35 µs
Switch off delay max.	400 µs
Voltage switching DC min.	5 V
Switching voltage DC max.	48 V
Switching current	0,1 mA
Switching current	0,5 A
Switching frequency ohmic	1.000 Hz
Switching frequency inductive max.	100 Hz
Diagnostics	
Status indication LED	yellow
Device protection | Electrical	
Rated insulation voltage	3.750 V
Device protection | Media	
Flame resistance	flame retardant
Mechanical data | Material data	
housing	Plastic
Color housing	black
Mechanical data | Mounting data	

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-09-14

Height	78 mm
Width	6,2 mm
Depth	70 mm
Mounting method	geschnappt
Suitable for mounting type	(EN 60715), mounting rail
Environmental characteristics | Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	60 °C
Connection type 4-4	
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	13 +
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	14
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	A 1
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	A 2

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-09-14